


# 126 Stainless Steel Board Retainer

## CATALOG NUMBER

**126-06-3.25**



The Series 126 is an economical PCB retention solution for sheet metal applications. Constructed of rugged stainless steel, the independent spring design provides board retention for low shock and vibration applications.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

## CERTIFICATIONS



## FEATURES

Length 31.75 mm (1.25") to 311.15 mm (12.25"), 24.5 mm (1.0") increments

Weight 0.48g/cm (0.043 oz/")

For sheet metal applications

Made from stainless steel

Supports PCB thickness of 1.6 mm (0.063") or 2.4 mm (0.094")

Spring based retention design

PRODUCT ATTRIBUTES

|                                  |
|----------------------------------|
| Product Type: PCB Retainer       |
| Material: Stainless Steel        |
| Type: PCB Tainer (Spring Design) |
| Finish: Passivated               |

ADDITIONAL PRODUCT DETAILS

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

| North America                                            | Europe                                                   | Asia                                                     | Middle East & India                                      |
|----------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|
| All locations                                            | Straubenhardt, Germany                                   | Shanghai, China                                          | Dubai, United Arab Emirates                              |
| +1.763.422.2661                                          | +49.7082.794.0                                           | +86.21.2412.6943                                         | +971.4.378.1700                                          |
| Chat with us:                                            | Betschdorf, France                                       | Qingdao, China                                           | Bangalore, India                                         |
| <a href="http://nvent.com/schroff">nvent.com/schroff</a> | +33.3.88.90.64.90                                        | +86.532.8771.6101                                        | +91.80.6715.2001                                         |
|                                                          | Warsaw, Poland                                           | Singapore                                                | Istanbul, Turkey                                         |
|                                                          | +48.22.209.98.35                                         | +65.6768.5800                                            | +90.216.250.7374                                         |
|                                                          | Assago, Italy                                            | Shin-Yokohama, Japan                                     | Chat with us:                                            |
|                                                          | +39.02.932.7141                                          | +81.45.476.0271                                          | <a href="http://nvent.com/schroff">nvent.com/schroff</a> |
|                                                          | Chat with us:                                            | Chat with us:                                            |                                                          |
|                                                          | <a href="http://nvent.com/schroff">nvent.com/schroff</a> | <a href="http://nvent.com/schroff">nvent.com/schroff</a> |                                                          |



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE