


Air Baffle, Front Panel, Retrofit Shielding, Steel



The air baffle with flat front panel covers an empty slot and eliminates an air leak. The flat front panel accepts a stainless steel EMC gasket.

CERTIFICATIONS



FEATURES

Air baffle eliminates air leaks from empty slots

Cover is pushed into the guide rail

SPECIFICATIONS

Product Type:	Air Baffle
Material:	Aluminum
Finish:	Anodized; Passivated
Product Family:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
Type:	With Front Panel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Depth	EMC Shielding	Rack Width	Works With
20848-712	3U	1	160mm	No (Retrofittable)	4HP	Subracks, Cases

CatalogNumber	Rack Height	Package Quantity	Depth	EMC Shielding	Rack Width	Works With
20848-721	6U	1	220mm	No (Retrofittable)	4HP	Subracks, Cases
20848-713	3U	1	220mm	No (Retrofittable)	4HP	Subracks, Cases
20848-720	6U	1	160mm	No (Retrofittable)	4HP	Subracks, Cases

Table 2/2

Catalog Number	Quick Ship
20848-712	No
20848-721	No
20848-713	No
20848-720	No

ADDITIONAL PRODUCT DETAILS

Air baffle for 280 mm deep and for 80 mm rear I/O boards available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE