

# AMC Filler Module With Pull-Handle



This AdvancedMC filler module consists of a stainless steel front panel without LEDs and has EMC gaskets on the left hand and bottom side. The filler module is fixed into the chassis card guide by a snap in plastic nose. The module can be used to cover an empty slot, to ensure EMC shielding and close the front to seal air leaks into the chassis. These filler modules can be used in AdvancedMC Carriers and in MicroTCA slots. It doesn't require a locking bar.

## CERTIFICATIONS



## FEATURES

In accordance with AMC.0 R2.0 specification

Shielded filler modules are used to close unused slots

pull handle to extract sub-assembly

The optional air baffle (airflow adjustable) can be used to direct chassis airflow

## SPECIFICATIONS

**Product Family:** AdvancedMC  
**Type:** Filler Module  
**Product Type:** System Module

Table 1/1

| Catalog Number | Design Feature | Material        | Finish     | Package Quantity | Quick Ship |
|----------------|----------------|-----------------|------------|------------------|------------|
| 20849-248      | Mid-Size       | Aluminum        | Passivated | 1                | No         |
| 20849-024      | Full-Size      | Stainless Steel |            | 1                | No         |

| Catalog Number | Design Feature | Material        | Finish     | Package Quantity | Quick Ship |
|----------------|----------------|-----------------|------------|------------------|------------|
| 20849-022      | Compact        | Stainless Steel |            | 1                | No         |
| 20849-250      | Full-Size      | Aluminum        | Passivated | 1                | No         |
| 20849-106      | Mid-Size       | Stainless Steel |            | 1                | No         |
| 20849-251      | Full-Size      | Aluminum        | Passivated | 1                | No         |
| 20849-107      | Mid-Size       | Stainless Steel |            | 1                | No         |
| 20849-025      | Full-Size      | Stainless Steel |            | 1                | No         |
| 20849-249      | Mid-Size       | Aluminum        | Passivated | 1                | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**