

# nVent CADDY Cat 425 Adjustable Cable Support with Flange Clip



## CERTIFICATIONS



## FEATURES

Requires only a hammer to install

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Simple unlocking and locking of bar allows for additional cables to be added easily after installation

Adjustable strap allows for multiple support sizes to reduce inventory

Cost effective alternative to expensive cable tray

cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems

Suitable for air handling spaces (plenum)

## SPECIFICATIONS

**Finish:** nVent CADDY Armour;Electrogalvanized

**Material:** Steel;Polyethylene;Spring Steel

Table 1/2


Catalog Number	Article Number	Diameter (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A
----------------	----------------	--------------	------	------------------------	-----------------------	------------------------

CAT42524SM	181620	100 mm, 150 mm	13181mm <sup>2</sup>	425	325	210
CAT42558SM	181630	100 mm, 150 mm	13181mm <sup>2</sup>	425	325	210
CAT425912SM	181640	100 mm, 150 mm	13181mm <sup>2</sup>	425	325	210

Table 2/2

Catalog Number	Article Number	Flange Thickness (FT)	Static Load
CAT42524SM	181620	3.2 - 6.4 mm	450N
CAT42558SM	181630	7.9 - 12.7 mm	450N
CAT425912SM	181640	14.3 - 19.1 mm	450N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

