We connect and protect

PXI Express Controller, 4 HP, I3-1115G4E 16-512

CATALOG NUMBER

21265-120

The nVent SCHROFF PXIe embedded controller is the most compact and powerful 3U one-slot embedded controller for the PXI Express and CPCIexp platforms. With its huge and future-ready interface capabilities, it runs perfectly with most test and measurement applications. The Controller is driven by a 11th generation Intel® Core™ i3 / i5 processors combined with up to 64GB DDR4 memory and easily supports high bandwidth applications with future ready PCIe Gen4 and dual 2500BASE-T system interconnectivity.

FEATURES

- PXI Express System Controller, 3 U, 4 HP, with Intel Core I3-1115G4E Processor
- PXI™-5 PXI Express hardware spec. Rev.2.0 compliant
- Maximum 14 GB/s PCIe Bandwidth
- Upgradeable m.2 NVMe and DDR4 Storage
- 3x USB3.1, 2x GbE and 1x DP 1.2 on the front panel
- Full customizable AMI Aptio® Embedded BIOS

PRODUCT ATTRIBUTES

- Product Type: System
- Type: Controller
- Data Transfer: PCIe Gen3
- Rack Height: 3U
- Complies With: PXISA PXI-5 R1.1
- Depth: 160mm
- Gross Weight: 0.548kg
- Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Conform to PICMG rev. 3.0 and PXI-5.

Modified Controllers available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.