

Vertical Cable Manager for 700- and 800-mm Wide Cabinets

Data Solutions



The Vertical Cable Manager for 700- and 800-mm Wide Cabinets are used for routing and bundling cable inside 700- and 800-mm wide ProLine cabinets. This product has a variety of sizes that provides mounting flexibility. It mounts between the frame and rack angles so equipment can be centered or aligned on one side. It replaces reducing brackets that bridge space between cabinet and equipment and allows front-to-back adjustment of the rack angles. The latching hinged door on the front conceals wiring yet allows easy access while the movable plastic spools help manage cables.

FEATURES

The Vertical Cable Manager for 700- and 800-mm Wide Cabinets are used for routing and bundling cable inside 700- and 800-mm wide ProLine cabinets

This product has a variety of sizes that provides mounting flexibility. It mounts between the frame and rack angles so equipment can be centered or aligned on one side

It replaces reducing brackets that bridge space between cabinet and equipment and allows front-to-back adjustment of the rack angles

The latching hinged door on the front conceals wiring yet allows easy access while the movable plastic spools help manage cables

SPECIFICATIONS

Color:	Jet Black
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 9005

Table 1/1

Catalog Number	Article Number	Thickness	Fits Cabinet Height
PVCM167	10973	1.9mm	1600mm

Catalog Number	Article Number	Thickness	Fits Cabinet Height
PVCM168	10977	1.9mm	1600mm
PVCM187	10974	1.9mm	1800mm
PVCM188	10978	1.9mm	1800mm
PVCM207	10975	1.9mm	2000mm
PVCM208	10981	1.9mm	2000mm
PVCM227	10976	1.9mm	2200mm
PVCM228	10982	1.9mm	2200mm
PVCMX127	16016	1.9mm	1200mm, 2200mm
PVCMX128	16017	1.9mm	1200mm, 2200mm
PVCMX207	16018	1.9mm	2000mm
PVCMX208	16021	1.9mm	2000mm

ADDITIONAL PRODUCT DETAILS

Use the "Cable Managers by Width" table to determine the number of cable managers required for different combinations of cable manager, cabinet and equipment widths.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE