


LHX+ Air/Liquid Heat Exchanger



RackChiller In-Row Coolers (IRC) are designed to deliver localized/supplemental energy efficient cooling in data centers. RackChiller IRC is a modular and scalable precision cooling solution that can replace or supplement traditional data center cooling infrastructure.

FEATURES

19" mountable Air/liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

SPECIFICATIONS

Depth: 500mm
Product Type: Air/Liquid Heat Exchanger
Airflow Direction: Front to Top

Table 1/2

Catalog Number	Fan Quantity	Input Voltage AC	Package Quantity	Supply Voltage	Redundant Power Supply	Coolant Feed
29714-017	1	100 – 240V	1	230V min	No	Bottom
29714-016	2	100 – 240V	1	230V min	No	Bottom

Table 2/2

Catalog Number	Height	Material	Product Family	Width	Works With	Quick Ship
29714-017	266mm	Aluminum	Cooling	426mm	Varistar, Varistar CP	No

CatalogNumber	Height	Material	Product Family	Width	Works With	Quick Ship
29714-016	266mm	Aluminum	Cooling	426mm	Varistar, Varistar CP	No

ADDITIONAL PRODUCT DETAILS

Please order separatly: Monitoring via Control unit, water control package, display and door contact switch.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE