

Insulated Mounting Panel, AMI



This is an easy to machine mounting plate that will prevent undesired contact between electrical components and the enclosure.

FEATURES

Description: Insulated mounting plate for wall mounted enclosures. By using the AMG accessory, the mounting plate position can be adjusted to any depth. This accessory is not suitable for the AFS range of enclosures, please refer to the replacement and spare parts catalogue.

Material: Bakelite.

Pack quantity: 1 piece.

SPECIFICATIONS

Thickness: 4mm
Material: Bakelite
Color: Black
Finish: Smooth

Table 1/1

Catalog Number	E-Number	Height	Width	Depth	Panel Size	Enclosure Material
AMI02020	2410961	200mm	200mm	4mm	170 x 150mm	Mild Steel
AMI02520	2410962	250mm	200mm	4mm	220 x 150mm	Mild Steel
AMI02525	2414300	250mm	250mm	4mm	220 x 200mm	Mild Steel
AMI03025	2414301	300mm	250mm	4mm	270 x 200mm	Mild Steel
AMI03030	2414302	300mm	300mm	4mm	270 x 250mm	Mild Steel
AMI03040		300mm	400mm	4mm	270 x 350mm	Mild Steel
AMI03525	2410963	350mm	250mm	4mm	320 x 200mm	Mild Steel
AMI04030	2414303	400mm	300mm	4mm	370 x 250mm	Mild Steel
AMI04040	2410964	400mm	400mm	4mm	370 x 350mm	Mild Steel
AMI04050	2410965	400mm	500mm	4mm	370 x 450mm	Mild Steel
AMI04060	2410966	400mm	600mm	4mm	370 x 550mm	Mild Steel
AMI05030	2414304	500mm	300mm	4mm	470 x 250mm	Mild Steel
AMI05040	2414305	500mm	400mm	4mm	470 x 350mm	Mild Steel
AMI05050	2410967	500mm	500mm	4mm	470 x 450mm	Mild Steel
AMI06040	2414306	600mm	400mm	4mm	570 x 350mm	Mild Steel
AMI06050	2414307	600mm	500mm	4mm	570 x 450mm	Mild Steel

Catalog Number	E-Number	Height	Width	Depth	Panel Size	EnclosureMaterial
AMI06060	2414308	600mm	600mm	4mm	570 x 550mm	Mild Steel
AMI06080	2410968	600mm	800mm	4mm	570 x 750mm	Mild Steel
AMI07050	2414309	700mm	500mm	4mm	670 x 450mm	Mild Steel
AMI08040	2410969	800mm	400mm	4mm	770 x 350mm	Mild Steel
AMI08060	2414310	800mm	600mm	4mm	770 x 550mm	Mild Steel
AMI08080	2410970	800mm	800mm	4mm	770 x 750mm	Mild Steel
AMI10060	2414311	1000mm	600mm	4mm	970 x 550mm	Mild Steel
AMI10080	2414312	1000mm	800mm	4mm	970 x 750mm	Mild Steel
AMI12060	2414313	1200mm	600mm	4mm	1170 x 550mm	Mild Steel
AMI12080	2414314	1200mm	800mm	4mm	1170 x 750mm	Mild Steel

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE