

Varistar CP Steel Door, Plain With 3-Point Locking, IP55

Power Utilities

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FEATURES

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Width	Color	Color Code	Complies With
21630-171	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-210	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-211	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-212	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-213	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-214	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-215	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-216	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

CatalogNumber	Rack Height	Height	Width	Color	Color Code	Complies With
21630-217	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-218	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-219	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-220	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Catalog Number	Finish	Locking Type	Material	Product Type	Protection Rating	Type
21630-171	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-210	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-211	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-212	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-213	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-214	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-215	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-216	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-217	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-218	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-219	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door
21630-220	Powder Coated	3-Point Locking	Steel	Cabinet Door	IP55	Steel Door

Table 3/3

Catalog Number	Works With
21630-171	Varistar CP
21630-210	Varistar CP
21630-211	Varistar CP
21630-212	Varistar CP
21630-213	Varistar CP
21630-214	Varistar CP
21630-215	Varistar CP
21630-216	Varistar CP
21630-217	Varistar CP
21630-218	Varistar CP
21630-219	Varistar CP
21630-220	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE