

# 24 Lok-Tainer

## CATALOG NUMBER

**24BX-2-10-3-L**



The Series 24 Lok Tainer is designed for sheet metal enclosure applications. It features a lever actuated cam and lobe design for tool-free PCB retention in moderate shock and vibration environments.

⚠ WARNING: This product can expose you to chemicals including beryllium, which is known to the State of California to cause cancer. For more information, go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

## CERTIFICATIONS



## FEATURES

Constructed from beryllium copper or steel

DSCC 84168

Lever actuation

Cam and lobe based retention design

Supports PCB thickness of 0.79 mm (0.031"), 1.6 mm (0.063"), or 2.4 mm (0.094")

Weight 0.97 g/cm (0.087 oz/")

Available unplated, or with silver, ebanol, copper, gold, nickel, zinc clear chromate, or zinc yellow chromate plating

For sheet metal applications

Length 31.75 mm (1.25") to 311.15 mm (12.25"), 24.5 mm (1.0") increments

PRODUCT ATTRIBUTES

Product Type: PCB Retainer

Material: Steel; Beryllium Copper

Type: PCB Lok-Tainer (Cam and Lobe Design)

ADDITIONAL PRODUCT DETAILS

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

Timing & availability of products containing Beryllium Copper material are subject to material availability and have lead times up to 52 weeks.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including beryllium, which is known to the State of California to cause cancer. For more information, go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

| North America                                            | Europe                                                   | Asia                                                     | Middle East & India                                      |
|----------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|
| All locations                                            | Straubenhardt, Germany                                   | Shanghai, China                                          | Dubai, United Arab Emirates                              |
| +1.763.422.2661                                          | +49.7082.794.0                                           | +86.21.2412.6943                                         | +971.4.378.1700                                          |
| Chat with us:                                            | Betschdorf, France                                       | Qingdao, China                                           | Bangalore, India                                         |
| <a href="http://nvent.com/schroff">nvent.com/schroff</a> | +33.3.88.90.64.90                                        | +86.532.8771.6101                                        | +91.80.6715.2001                                         |
|                                                          | Warsaw, Poland                                           | Singapore                                                | Istanbul, Turkey                                         |
|                                                          | +48.22.209.98.35                                         | +65.6768.5800                                            | +90.216.250.7374                                         |
|                                                          | Assago, Italy                                            | Shin-Yokohama, Japan                                     | Chat with us:                                            |
|                                                          | +39.02.932.7141                                          | +81.45.476.0271                                          | <a href="http://nvent.com/schroff">nvent.com/schroff</a> |
|                                                          | Chat with us:                                            | Chat with us:                                            |                                                          |
|                                                          | <a href="http://nvent.com/schroff">nvent.com/schroff</a> | <a href="http://nvent.com/schroff">nvent.com/schroff</a> |                                                          |



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE