

nVent CADDY Macrofix, Stainless Steel



FEATURES

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

SPECIFICATIONS

Finish:	Electropolished
Material:	Stainless Steel 316 (EN 1.4401);EPDM-SBR Rubber
Temperature:	-50 to 110 °C

Table 1/2

Catalog Number	Article Number	Outer Diameter (OD)	NB/DN	Rod Size (RS)	Width (W)	Thickness (T)
MXE019S6	595600	15 - 19 mm	10	M8	20 mm	1.5 mm
MXE080S6	595690	75 - 80 mm	65	M8	25 mm	2 mm
MXE086S6	595695	82 - 86 mm		M8	25 mm	2 mm
MXT091S6	595700	89 - 91 mm	80	M10	25 mm	2 mm
MXT127S6	595730	121 - 127 mm		M10	25 mm	2.5 mm

CatalogNumber	Article Number	Outer Diameter (OD)	NB/DN	Rod Size (RS)	Width (W)	Thickness (T)
MXT168S6	595760	165 - 168 mm	150	M10	25 mm	2.5 mm
MXT220S6	595780	216 - 220 mm	200	M10	30 mm	3 mm


Table 2/2

Catalog Number	Article Number	Screw Diameter (Sc)	Screw Length (L)	Static Load
MXE019S6	595600	6	20mm	1000N
MXE080S6	595690	6	25mm	1300N
MXE086S6	595695	6	25mm	1300N
MXT091S6	595700	6	25mm	1300N
MXT127S6	595730	6	25mm	2200N
MXT168S6	595760	6	25mm	2200N
MXT220S6	595780	8	25mm	2500N

ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

