

nVent CADDY Swift Clip Strut Clamp for Insulated Tube/Pipe



FEATURES

Secures pipe and insulation without a break, providing an uninterrupted vapor barrier seal which eliminates sweating on metal fittings

Snap-in and twist installation requires no tools

Fits directly into vertical and horizontal strut channels

For support and positioning of refrigeration, A/C tubing, PEX piping, conduit and cabling

Compliant with UL® 2043 and suitable for use in air handling (plenum) spaces

SPECIFICATIONS

Material: Polyamide

Working Temperature: -40 to 140 °C

Table 1/1

Catalog Number	Article Number	Outer Diameter (OD)	Copper Tube Size	NB/DN	Width (W)
TSMI0062	389057	15 mm	1/2"		41 mm
TSMI0087	389059	22 mm	3/4"	15	41 mm
TSMI0075	389058	20 mm	5/8"		41 mm


Catalog Number	Article Number	Outer Diameter (OD)	Copper Tube Size	NB/DN	Width (W)
TSMI0100	389061	25 mm		20	41 mm
TSMI0112	389062	28 mm	1"		41 mm
TSMI0125	389063	32 mm		25	41 mm
TSMI0137	389064	35 mm	1 1/4"		41 mm
TSMI0150	389065	40 mm			41 mm
TSMI0162	389066	42 mm	1 1/2"		41 mm
TSMI0200	389067	50 mm			41 mm
TSMI0212	389068	54 mm	2"		41 mm

ADDITIONAL PRODUCT DETAILS

Can also be used with PEX piping. For PEX pipe sizes, refer to the Copper Tube Size column.

Clip must be installed with temperature at or above 14 °F (-10 °C).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

