

Mounting Plate, MP



The steel mounting plate contributes to speeding up the assembly of the enclosure, since it can be machined easily and equipped with components before being mounted.

FEATURES

Description: Standard mounting plate. It can also be mounted on the side of an enclosure by using MPS kit or slid in from the side with the MTS profile. For heavy loads in vibrating environments use mounting plate reinforcement profile MPR and MPE or MPEF brackets.

Material: 3 mm galvanized steel.

Pack quantity: 1 piece.

Maximum load: 6000 N.

Mounting requirements: Use MPA for mounting the MP inside the enclosure. Adjustable in depth with MPD accessory.

SPECIFICATIONS

Thickness: 3mm
Finish: Galvanized
Material: Mild Steel

Table 1/1

Catalog Number	E-Number	Height	Width	Depth	Mounting Plate Height
MP1606	2418500	1600mm	600mm	25mm	1494mm
MP1608	2418501	1600mm	800mm	25mm	1494mm
MP1806	2418506	1800mm	600mm	25mm	1694mm
MP1808	2418507	1800mm	800mm	25mm	1694mm
MP2006	2418513	2000mm	600mm	25mm	1894mm
MP2008	2418515	2000mm	800mm	25mm	1894mm
MP1212	2411743	1200mm	1200mm	25mm	1094mm
MP1612	2418503	1600mm	1200mm	25mm	1494mm
MP1812	2418509	1800mm	1200mm	25mm	1694mm
MP1816	2418510	1800mm	1600mm	25mm	1694mm
MP2012	2418517	2000mm	1200mm	25mm	1894mm
MP2016	2418518	2000mm	1600mm	25mm	1894mm
MP1206	2411741	1200mm	600mm	25mm	1094mm
MP1208	2411742	1200mm	800mm	25mm	1094mm
MP1406	2411744	1400mm	600mm	25mm	1294mm
MP1408	2411745	1400mm	800mm	25mm	1294mm

Catalog Number	E-Number	Height	Width	Depth	Mounting PlateHeight
MP1610	2418502	1600mm	1000mm	25mm	1494mm
MP1810	2418508	1800mm	1000mm	25mm	1694mm
MP2010	2418516	2000mm	1000mm	25mm	1894mm
MP2210	2418521	2200mm	1000mm	25mm	2094mm
MP2212	2418522	2200mm	1200mm	25mm	2094mm
MP1804	2418504	1800mm	400mm	25mm	1694mm
MP1805	2418505	1800mm	500mm	25mm	1694mm
MP2004	2418511	2000mm	400mm	25mm	1894mm
MP2005	2418512	2000mm	500mm	25mm	1894mm
MP2206	2418519	2200mm	600mm	25mm	2094mm
MP2208	2418520	2200mm	800mm	25mm	2094mm
MP1410	2411746	1400mm	1000mm	25mm	1294mm
MP1412	2411747	1400mm	1200mm	25mm	1294mm

ADDITIONAL PRODUCT DETAILS

Note: for 1600 mm width, the mounting plate is delivered as two 800 mm width mounting plates and one filler plate.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE