

Plain Doors, DN



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

FEATURES

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMK (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

Maximum load: 800 N.

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNMK if no door was fitted previously.

Pack quantity: 1 piece.

SPECIFICATIONS

Color: Light Gray Material: Mild Steel Finish: **Powder Coated Color Code: RAL 7035**

Table 1/1 Enclosure **Catalog Number** E-Number Height Width Depth **Door Type** Material DN2210R5 2182mm 993mm Plain Mild Steel 17mm DN1106R5 1082mm 593mm 17mm Plain Mild Steel DN1206LR5 Left Door Mild Steel 2411164 1182mm 593mm 17mm DN1206R5 Plain Mild Steel 2411165 1182mm 593mm 17mm DN1206RR5 Mild Steel 2411166 1182mm 593mm 17mm Right Door DN1208R5 2411167 1182mm 793mm Plain Mild Steel 17mm DN1405LR5 2411168 1382mm 493mm 17mm Left Door Mild Steel DN1405RR5 2411169 1382mm 493mm 17mm Right Door Mild Steel DN1406LR5 2411170 1382mm 593mm 17mm Left Door Mild Steel DN1406R5 2411171 1382mm 593mm 17mm Plain Mild Steel DN1406RR5 793mm 17mm Mild Steel 2411172 1382mm Right Door DN1408R5 1382mm 793mm 17mm Plain Mild Steel DN1606LR5 1582mm 593mm 17mm Left Door Mild Steel DN1606R5 1582mm 593mm 17mm Plain Mild Steel DN1606RR5 Mild Steel 1582mm 593mm 17mm Right Door DN1608R5 1582mm 793mm 17mm Plain Mild Steel

Catalog Number	E-Number	Height	Width	Depth	Door Type	EnclosureMaterial
DN1610R5		1582mm	993mm	17mm	Plain	Mild Steel
DN1804LR5	2411175	1782mm	393mm	17mm	Left Door	Mild Steel
DN1804RR5	2411177	1782mm	393mm	17mm	Right Door	Mild Steel
DN1805LR5	2411178	1782mm	493mm	17mm	Left Door	Mild Steel
DN1805R5	2411179	1782mm	493mm	17mm	Plain	Mild Steel
DN1805RR5	2411180	1782mm	493mm	17mm	Right Door	Mild Steel
DN1806LR5	2411181	1782mm	593mm	17mm	Left Door	Mild Steel
DN1806R5	2411182	1782mm	593mm	17mm	Plain	Mild Steel
DN1806RR5	2411183	1782mm	593mm	17mm	Right Door	Mild Steel
DN1808LR5	2411184	1782mm	793mm	17mm	Left Door	Mild Steel
DN1808R5	2411185	1782mm	793mm	17mm	Plain	Mild Steel
DN1808RR5	2411186	1782mm	793mm	17mm	Right Door	Mild Steel
DN1810R5	2411187	1782mm	993mm	17mm	Plain	Mild Steel
DN2004LR5	2411188	1982mm	393mm	17mm	Left Door	Mild Steel
DN2004RR5	2411190	1982mm	393mm	17mm	Right Door	Mild Steel
DN2005LR5	2411191	1982mm	493mm	17mm	Left Door	Mild Steel
DN2005R5	2411192	1982mm	493mm	17mm	Plain	Mild Steel
DN2005RR5	2411193	1982mm	493mm	17mm	Right Door	Mild Steel
DN2006LR5	2411194	1982mm	593mm	17mm	Left Door	Mild Steel
DN2006R5	2411195	1982mm	593mm	17mm	Plain	Mild Steel

Catalog Number	E-Number	Height	Width	Depth	Door Type	EnclosureMaterial
DN2006RR5	2411196	1982mm	593mm	17mm	Right Door	Mild Steel
DN2008LR5	2411197	1982mm	793mm	17mm	Left Door	Mild Steel
DN2008R5	2411198	1982mm	793mm	17mm	Plain	Mild Steel
DN2008RR5	2411199	1982mm	793mm	17mm	Right Door	Mild Steel
DN2010R5	2411200	1982mm	993mm	17mm	Plain	Mild Steel
DN2205LR5	2411202	2182mm	493mm	17mm	Left Door	Mild Steel
DN2205RR5	2411203	2182mm	493mm	17mm	Right Door	Mild Steel
DN2206LR5	2411204	2182mm	593mm	17mm	Left Door	Mild Steel
DN2206R5	2411205	2182mm	593mm	17mm	Plain	Mild Steel
DN2206RR5	2411206	2182mm	593mm	17mm	Right Door	Mild Steel
DN2208R5	2411207	2182mm	793mm	17mm	Plain	Mild Steel
DN1804R5		1782mm	393mm	17mm	Plain	Mild Steel
DN2004R5		1982mm	393mm	17mm	Plain	Mild Steel
DN2204R5		2182mm	393mm	17mm	Plain	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY **ERICO HOFFMAN TRACHTE SCHROFF ILSCO**