

# RackChiller Rear Door Water Control Package, Active or Passive

## CATALOG NUMBER

**23130-608**



The stainless steel pipe inserts with ID 1" each come with a pair of ratiometric liquid coolant sensors. The sensors connect directly to the RackChiller Rear Door Controller. This enables monitoring of the coolant thermal properties and cooling performance, as well as additional temperature control features.

## CERTIFICATIONS



## FEATURES

Water control unit with water flow, pressure and temperature sensors

Supply sensors: coolant pressure and temperature

Return sensors: coolant flow and temperatures

Enables the controller to modulate the flow based on return temperature or coolant temperature differential

Prepared for perfect fit to RackChiller Rear Door and accessories

Both pipe inserts made of stainless steel

## PRODUCT ATTRIBUTES

Product Type: Connector Kit

Net Weight: 2.575kg

ADDITIONAL PRODUCT DETAILS

RackChiller Rear Door Controller required. This is included in the Active version, please use 21130-594 for Passive version.

For trouble-free operation it is recommended to use the water connection set and the optional accessories.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE