

FroStop Self-Regulating Heating Cable

nVent RAYCHEM Frostop self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection and roof and gutter de-icing.



FEATURES

Simple to design

Easy to install: cut to length, meter marks

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no overheating possible

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Table 1/4

Catalog Number	Item Name	E-Number	Supply Voltage	Nominal Voltage	Nominal Power Output @ 5°C, 230V	Outer Jacket Material
559303-000	FROSTOP-BLACK-RANDOM	1038230	220 – 240 V	220 V, 230 V, 240 V	18 W/m	Modified Polyolefin

Table 2/4

Catalog Number	Item Name	E-Number	Max Circuit Length	Color	Nominal Width	Nominal Height
559303-000	FROSTOP-BLACK-RANDOM	1038230	80 m	Black	10.5 mm	5.5 mm

Table 3/4

Catalog Number	Item Name	E-Number	Ground Path Type	Min Installation Temperature	Conductor Material	Min Bending Radius
----------------	-----------	----------	------------------	------------------------------	--------------------	--------------------

559303-000	FROSTOP- BLACK- RANDOM	1038230	Braid	-18 °C	Nickel-Plated Copper	10 mm
------------	------------------------------	---------	-------	--------	-------------------------	-------

Table 4/4

Catalog Number	Item Name	E-Number	Nominal Thickness
559303-000	FROSTOP-BLACK-RANDOM	1038230	5.5 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT