

HWAT Self-Regulating Heating Cable



nVent RAYCHEM HWAT self-regulating trace heating cables maintain water temperatures in a building's hot water distribution network. Installed underneath the thermal insulation, they automatically compensate for pipe heat losses where they occur and provide an energy efficient solution.

FEATURES

Simple to design: single pipe instead of recirculation system

Branch lines, instant hot water at tap: for reduced tap times and water waste, water maintained at specific temperatures, no return pipework or return of cold water into the water heater

Easy to install: cut to length, meter marks, simple fast RayClic connections

Energy efficient and safe: no overheating, advanced energy saving and monitoring with HWAT-ECO or ACS-30 controller

Reliable during long life: 10 year product warranty available, aluminum foil layer to protect from chemical ingress, maintenance free

SPECIFICATIONS

Ground Path Type:	Braid
Outer Jacket Material:	Modified Polyolefin
Conductor Material:	Nickel-Plated Copper

Table 1/2

Catalog Number	Item Name	E-Number	Supply Voltage	Color	Max Circuit Length	Nominal Width
498639-000	HWAT-M	1038209	220 – 240 V	Orange	100 m	13.7 mm
258015-000	HWAT-L	1038208	220 – 240 V	Yellow	180 m	13.8 mm
266435-000	HWAT-R	1038210	220 – 240 V	Red	100 m	16.1 mm

Table 2/2

Catalog Number	Item Name	E-Number	Nominal Thickness
498639-000	HWAT-M	1038209	7.6 mm
258015-000	HWAT-L	1038208	6.8 mm
266435-000	HWAT-R	1038210	6.7 mm

ADDITIONAL PRODUCT DETAILS

Requires the use of a 30 mA residual current device (RCD) to provide maximum safety and protection from fire. All heating circuits have to be protected by C-type circuit breaker.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT