nVent | SCHROFF

We connect and protect

CPCI Power Backplane With P 47 Connector, 6 U, 8 HP, 2x P47

CATALOG NUMBER

23098-396



Power Backplane for CompactPCI Applications. With P47 Power Connector.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- In accordance with: PICMG 2.11 R1.0 CompactPCI Power Interface specification
- In accordance with: PICMG 2.9 R1.0 System Management Bus specification
- Single, parallel or redundant operation possible
- Geographical address adjustable
- Power supply over crimp contacts inserted into the plug, no supply voltage on the backplane
- Power cable available as an accessory
- DC outlets with powerbugs for extremely low drops in voltage

PRODUCT ATTRIBUTES

- Product Type: Backplane
- Number of Slots: 1
- Rack Height: 6U

Backplane Type: CompactPCI Power Backplane with P47
Slot Width: 8HP
Power Connector Type: (2) P47
Utility Connector Type: SMCQ, 12-pin; MicroMatch, 10-pin
Width: 39.6mm
Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.