

# ProLine G2 Joining Subpanels



The ProLine G2 Joining Subpanel provides a continuous panel surface in multiple-bay enclosures. The joining subpanel is inserted between full subpanels of equal height. It can be installed from front or rear.

## FEATURES

---

Provides a continuous panel surface in multiple bay enclosures

Can be inserted between full mounting subpanels of equal height

Painted or galvanized options

Can be installed from front or rear

Subpanels can be mounted at any depth in 25-mm increments (front to back)

## SPECIFICATIONS

| Table 1/1      |                |            |               |       |           |            |
|----------------|----------------|------------|---------------|-------|-----------|------------|
| Catalog Number | Article Number | Material   | Finish        | Color | Thickness | Quick Ship |
| P2PJ10         | 32485          | Mild Steel | Powder Coated | White | 2.66mm    | No         |
| P2PJ10G        | 32484          | Mild Steel | Galvanized    | White | 2.66mm    | No         |
| P2PJ12         | 32487          | Mild Steel | Powder Coated | White | 2.66mm    | No         |
| P2PJ12G        | 32486          | Mild Steel | Galvanized    | White | 2.66mm    | No         |
| P2PJ6          | 32504          | Mild Steel | Powder Coated | White | 2.66mm    | No         |
| P2PJ6G         | 32503          | Mild Steel | Galvanized    | White | 2.66mm    | No         |
| P2PJ8          | 32506          | Mild Steel | Powder Coated | White | 2.66mm    | No         |
| P2PJ8G         | 32505          | Mild Steel | Galvanized    | White | 2.66mm    | No         |
| P2PJ14         | 32491          | Mild Steel | Powder Coated | White | 3.4mm     | No         |
| P2PJ14G        | 32488          | Mild Steel | Galvanized    | White | 3.4mm     | No         |
| P2PJ16         | 32493          | Mild Steel | Powder Coated | White | 3.4mm     | No         |
| P2PJ16G        | 32492          | Mild Steel | Galvanized    | White | 3.4mm     | No         |
| P2PJ18         | 32495          | Mild Steel | Powder Coated | White | 3.4mm     | No         |
| P2PJ18G        | 32494          | Mild Steel | Galvanized    | White | 3.4mm     | No         |
| P2PJ20         | 32497          | Mild Steel | Powder Coated | White | 3.4mm     | No         |
| P2PJ20G        | 32496          | Mild Steel | Galvanized    | White | 3.4mm     | No         |
| P2PJ22         | 32502          | Mild Steel | Powder Coated | White | 3.4mm     | No         |
| P2PJ22G        | 32498          | Mild Steel | Galvanized    | White | 3.4mm     | No         |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**