



Telecom Grounding Busbar

Data Solutions



CERTIFICATIONS



FEATURES

Meets TIA-607-C and TIA-607-D conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICATIONS

Thickness (T): 6.35mm

Width (W): 50.8mm

Material: Copper

Table 1/2


Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number of Pairs	Hole Size 2 (HS2)
----------------	-------------	---------------	---------------	-------------------	-----------------------------	-------------------

TGBA12L06P	No	305mm	229mm	8mm	6	11mm
TGBA12L06PT	Yes	305mm	229mm	8mm	6	11mm
TGBA16L08P	No	394mm	229mm	8mm	8	11mm
TGBA16L08PT	Yes	394mm	229mm	8mm	8	11mm
TGBA18L10P	No	451mm	229mm	8mm	10	11mm
TGBA18L10PT	Yes	451mm	229mm	8mm	10	11mm
TGBA20L12P	No	508mm	229mm	8mm	12	11mm
TGBA20L12PT	Yes	508mm	229mm	8mm	12	11mm
TGBA24L14P	No	610mm	457mm	8mm	14	11mm
TGBA24L14PT	Yes	610mm	457mm	8mm	14	11mm
TGBA29L18P	No	737mm	457mm	8mm	18	11mm
TGBA29L18PT	Yes	737mm	457mm	8mm	18	11mm

Table 2/2				
Catalog Number	Hole Size 2 Number of Pairs	A	B	C
TGBA12L06P	3	25.4mm	28.6mm	15.9mm
TGBA12L06PT	3	25.4mm	28.6mm	15.9mm
TGBA16L08P	3	25.4mm	28.6mm	15.9mm
TGBA16L08PT	3	25.4mm	28.6mm	15.9mm
TGBA18L10P	3	25.4mm	28.6mm	15.9mm

Catalog Number	Hole Size 2 Number of Pairs	A	B	C
TGBA18L10PT	3	25.4mm	28.6mm	15.9mm
TGBA20L12P	3	25.4mm	28.6mm	15.9mm
TGBA20L12PT	3	25.4mm	28.6mm	15.9mm
TGBA24L14P	5	25.4mm	28.6mm	15.9mm
TGBA24L14PT	5	25.4mm	28.6mm	15.9mm
TGBA29L18P	5	25.4mm	28.6mm	15.9mm
TGBA29L18PT	5	25.4mm	28.6mm	15.9mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE