

## Depth Extension Kit, UDE



The extension frame will allow for components that do not fit within the standard depth of the enclosure to be mounted.

### FEATURES

Description: Increases the standard depth (320 mm) of the enclosure up to 640 mm. When this accessory is used the rain hood cannot be used. UDE maintains the enclosures IP rating.

Finish: RAL 7035.

Delivery: 2 side panels, one top and one bottom panel, two open back panels and mounting accessories.

Delivery: 2 side panels, one top and one bottom panel, two open back panels and mounting accessories

Polyester depth extension frame for polyester modular wall mounted enclosures

The extension frame increases the depth of the standard enclosure by 55 mm and is mounted between the enclosure's door and body

Components that do not fit within the standard depth can be installed thanks to the increase in the enclosure's depth

The extension frame can be easily mounted at the last minute

SPECIFICATIONS

**Color:** Light Gray  
**Material:** Polyester  
**Color Code:** RAL 7035  
**Finish:** Smooth

| Table 1/1      |        |        |                    |                |            |
|----------------|--------|--------|--------------------|----------------|------------|
| Catalog Number | Height | Width  | Enclosure Material | Product Family | Quick Ship |
| UDE75100       | 750mm  | 100mm  | Polyester          | Wall Mounted   | No         |
| UDE10050       | 1000mm | 500mm  | Polyester          | Wall Mounted   | No         |
| UDE7550        | 750mm  | 500mm  | Polyester          | Wall Mounted   | No         |
| UDE7575        | 750mm  | 750mm  | Polyester          | Wall Mounted   | No         |
| UDE75125       | 750mm  | 1250mm | Polyester          | Wall Mounted   | No         |
| UDE12575       | 1250mm | 750mm  | Polyester          | Wall Mounted   | No         |
| UDE10075       | 1000mm | 750mm  | Polyester          | Wall Mounted   | No         |
| UDE100100      | 1000mm | 1000mm | Polyester          | Wall Mounted   | No         |
| UDE100125      | 1000mm | 1249mm | Polyester          | Wall Mounted   | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**