

# Front Cover Profiles For Power Distribution, MSFCP



The mild steel frame for front panels, MSFCP, is a flexible solution that allows for the creation of a customized power distribution enclosure with plain and/or slotted front panels. The frame enhances both the aesthetics of the enclosure as well as operator safety.

## FEATURES

Description: Front frame built up by two vertical and two horizontal profiles. To be covered by front panels MSMBP or MSMCP.

Material: 1.5 mm galvanized steel.

Finish: RAL 7035 structured powder coating.

Delivery: 2 vertical profiles, top and bottom profiles, and mounting material.

The frame provides customers with a flexible solution, as it can be adapted especially for their components using both plain and slotted cover plates

The plates ensure that both modular and non-modular components can be installed into the same enclosure

The frame improves the aesthetics of the enclosure while providing a safe solution for operators, even when the external door is open

Plain (MSMBP) and/or slotted (MSMCP) front panels must be mounted, in order to completely cover the front of the frame

SPECIFICATIONS

Thickness: 1.5mm  
Finish: Galvanized  
Material: Steel

| Table 1/1      |        |       |               |                    |                |            |
|----------------|--------|-------|---------------|--------------------|----------------|------------|
| Catalog Number | Height | Width | Usable Height | Enclosure Material | Product Family | Quick Ship |
| MSFCP1808R5    | 1800mm | 800mm | 1700mm        | Mild Steel         | Free-Standing  | No         |
| MSFCP2208R5    | 2200mm | 800mm | 2100mm        | Mild Steel         | Free-Standing  | No         |
| MSFCP2006R5    | 2000mm | 600mm | 1900mm        | Mild Steel         | Free-Standing  | No         |
| MSFCP2206R5    | 2200mm | 600mm | 2100mm        | Mild Steel         | Free-Standing  | No         |
| MSFCP1806R5    | 1800mm | 600mm | 1700mm        | Mild Steel         | Free-Standing  | No         |
| MSFCP2008R5    | 2000mm | 800mm | 1900mm        | Mild Steel         | Free-Standing  | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE