


# Novastar Side Panel for Slim-Line

## Power Utilities



Steel Side Panels for Slim.Line aluminum frame with quick fastner for easy mounting and installation. Schroff delivers cladding parts with grounding cable installed and tested

## CERTIFICATIONS



## FEATURES

Side panel with quarter-turn fastener, includes grounding

St, 1 mm

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height | Depth  | Color      | Color Code | Product Type       |
|----------------|-------------|--------|--------|------------|------------|--------------------|
| 25230-070      | 6 U         | 357 mm | 500 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |

| CatalogNumber | Rack Height | Height | Depth   | Color      | Color Code | Product Type       |
|---------------|-------------|--------|---------|------------|------------|--------------------|
| 25230-120     | 6 U         | 357 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-070     | 6 U         | 357 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-120     | 6 U         | 357 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-071     | 9 U         | 490 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-121     | 9 U         | 490 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-071     | 9 U         | 490 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-121     | 9 U         | 490 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-072     | 12 U        | 589 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-113     | 12 U        | 531 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-114     | 12 U        | 531 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-122     | 12 U        | 589 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-172     | 12 U        | 589 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-072     | 12 U        | 589 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-113     | 12 U        | 531 mm | 900 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-114     | 12 U        | 531 mm | 1000 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-122     | 12 U        | 589 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-172     | 12 U        | 589 mm | 800 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-073     | 16 U        | 709 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |

| CatalogNumber | Rack Height | Height | Depth   | Color      | Color Code | Product Type       |
|---------------|-------------|--------|---------|------------|------------|--------------------|
| 25230-115     | 16 U        | 709 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-116     | 16 U        | 709 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-123     | 16 U        | 709 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-173     | 16 U        | 709 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-073     | 16 U        | 709 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-115     | 16 U        | 709 mm | 900 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-116     | 16 U        | 709 mm | 1000 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-123     | 16 U        | 709 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-173     | 16 U        | 709 mm | 800 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-074     | 20 U        | 945 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-117     | 20 U        | 887 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-118     | 20 U        | 887 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-124     | 20 U        | 945 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-174     | 20 U        | 945 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-074     | 20 U        | 945 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-117     | 20 U        | 887 mm | 900 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-118     | 20 U        | 887 mm | 1000 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-124     | 20 U        | 945 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |

| CatalogNumber | Rack Height | Height  | Depth   | Color      | Color Code | Product Type       |
|---------------|-------------|---------|---------|------------|------------|--------------------|
| 26230-174     | 20 U        | 945 mm  | 800 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-075     | 25 U        | 1167 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-119     | 25 U        | 1109 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-125     | 25 U        | 1167 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-130     | 25 U        | 1109 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-175     | 25 U        | 1167 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-075     | 25 U        | 1167 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-119     | 25 U        | 1109 mm | 900 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-125     | 25 U        | 1167 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-130     | 25 U        | 1109 mm | 1000 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-175     | 25 U        | 1167 mm | 800 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-076     | 34 U        | 1567 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-126     | 34 U        | 1567 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-131     | 34 U        | 1509 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-132     | 34 U        | 1509 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-176     | 34 U        | 1567 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-076     | 34 U        | 1567 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-126     | 34 U        | 1567 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |

| CatalogNumber | Rack Height | Height  | Depth   | Color      | Color Code | Product Type       |
|---------------|-------------|---------|---------|------------|------------|--------------------|
| 26230-131     | 34 U        | 1509 mm | 900 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-132     | 34 U        | 1509 mm | 1000 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-176     | 34 U        | 1567 mm | 800 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-077     | 38 U        | 1745 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-127     | 38 U        | 1745 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-133     | 38 U        | 1687 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-134     | 38 U        | 1687 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-177     | 38 U        | 1745 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-077     | 38 U        | 1745 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-127     | 38 U        | 1745 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-133     | 38 U        | 1687 mm | 900 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-134     | 38 U        | 1687 mm | 1000 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-177     | 38 U        | 1745 mm | 800 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-078     | 43 U        | 1967 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-128     | 43 U        | 1967 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-135     | 43 U        | 1909 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-136     | 43 U        | 1909 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-178     | 43 U        | 1967 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |

| CatalogNumber | Rack Height | Height  | Depth   | Color      | Color Code | Product Type       |
|---------------|-------------|---------|---------|------------|------------|--------------------|
| 26230-078     | 43 U        | 1967 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-128     | 43 U        | 1967 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-135     | 43 U        | 1909 mm | 900 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-136     | 43 U        | 1909 mm | 1000 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-178     | 43 U        | 1967 mm | 800 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-079     | 47 U        | 2145 mm | 500 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-129     | 47 U        | 2145 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-137     | 47 U        | 2087 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-138     | 47 U        | 2087 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 25230-179     | 47 U        | 2145 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-079     | 47 U        | 2145 mm | 500 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-129     | 47 U        | 2145 mm | 600 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-137     | 47 U        | 2087 mm | 900 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-138     | 47 U        | 2087 mm | 1000 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 26230-179     | 47 U        | 2145 mm | 800 mm  | Light Grey | RAL 7035   | Cabinet/Rack Panel |

Table 2/2

| Catalog Number | Type       |
|----------------|------------|
| 25230-070      | Side Panel |
| 25230-120      | Side Panel |

| Catalog Number | Type       |
|----------------|------------|
| 26230-070      | Side Panel |
| 26230-120      | Side Panel |
| 25230-071      | Side Panel |
| 25230-121      | Side Panel |
| 26230-071      | Side Panel |
| 26230-121      | Side Panel |
| 25230-072      | Side Panel |
| 25230-113      | Side Panel |
| 25230-114      | Side Panel |
| 25230-122      | Side Panel |
| 25230-172      | Side Panel |
| 26230-072      | Side Panel |
| 26230-113      | Side Panel |
| 26230-114      | Side Panel |
| 26230-122      | Side Panel |
| 26230-172      | Side Panel |
| 25230-073      | Side Panel |
| 25230-115      | Side Panel |

| Catalog Number | Type       |
|----------------|------------|
| 25230-116      | Side Panel |
| 25230-123      | Side Panel |
| 25230-173      | Side Panel |
| 26230-073      | Side Panel |
| 26230-115      | Side Panel |
| 26230-116      | Side Panel |
| 26230-123      | Side Panel |
| 26230-173      | Side Panel |
| 25230-074      | Side Panel |
| 25230-117      | Side Panel |
| 25230-118      | Side Panel |
| 25230-124      | Side Panel |
| 25230-174      | Side Panel |
| 26230-074      | Side Panel |
| 26230-117      | Side Panel |
| 26230-118      | Side Panel |
| 26230-124      | Side Panel |
| 26230-174      | Side Panel |



| Catalog Number | Type       |
|----------------|------------|
| 25230-075      | Side Panel |
| 25230-119      | Side Panel |
| 25230-125      | Side Panel |
| 25230-130      | Side Panel |
| 25230-175      | Side Panel |
| 26230-075      | Side Panel |
| 26230-119      | Side Panel |
| 26230-125      | Side Panel |
| 26230-130      | Side Panel |
| 26230-175      | Side Panel |
| 25230-076      | Side Panel |
| 25230-126      | Side Panel |
| 25230-131      | Side Panel |
| 25230-132      | Side Panel |
| 25230-176      | Side Panel |
| 26230-076      | Side Panel |
| 26230-126      | Side Panel |
| 26230-131      | Side Panel |

| Catalog Number | Type       |
|----------------|------------|
| 26230-132      | Side Panel |
| 26230-176      | Side Panel |
| 25230-077      | Side Panel |
| 25230-127      | Side Panel |
| 25230-133      | Side Panel |
| 25230-134      | Side Panel |
| 25230-177      | Side Panel |
| 26230-077      | Side Panel |
| 26230-127      | Side Panel |
| 26230-133      | Side Panel |
| 26230-134      | Side Panel |
| 26230-177      | Side Panel |
| 25230-078      | Side Panel |
| 25230-128      | Side Panel |
| 25230-135      | Side Panel |
| 25230-136      | Side Panel |
| 25230-178      | Side Panel |
| 26230-078      | Side Panel |

| Catalog Number | Type       |
|----------------|------------|
| 26230-128      | Side Panel |
| 26230-135      | Side Panel |
| 26230-136      | Side Panel |
| 26230-178      | Side Panel |
| 25230-079      | Side Panel |
| 25230-129      | Side Panel |
| 25230-137      | Side Panel |
| 25230-138      | Side Panel |
| 25230-179      | Side Panel |
| 26230-079      | Side Panel |
| 26230-129      | Side Panel |
| 26230-137      | Side Panel |
| 26230-138      | Side Panel |
| 26230-179      | Side Panel |

## ADDITIONAL PRODUCT DETAILS

Optionally the quarter-turn fastener can be fitted with a side panel lock.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**