

# Varistar CP Double Steel Door, Plain, 3-Point Locking

## Data Solutions



Perforated Varistar CP steel double door with 3-point locking for applications with IP 20 protection.

### FEATURES

Double steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

### SPECIFICATIONS

|                           |                 |
|---------------------------|-----------------|
| <b>Locking Type:</b>      | 3-Point Locking |
| <b>Product Type:</b>      | Cabinet Door    |
| <b>Protection Rating:</b> | IP20            |
| <b>Material:</b>          | Steel           |

Table 1/2

| Catalog Number | Rack Height | Height | Width | Package Quantity | Color      | Color Code |
|----------------|-------------|--------|-------|------------------|------------|------------|
| 21630-086      | 42U         | 2000mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-087      | 47U         | 2200mm | 600mm | 1                | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height | Width | Package Quantity | Color      | Color Code |
|---------------|-------------|--------|-------|------------------|------------|------------|
| 21630-088     | 52U         | 2450mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-089     | 42U         | 2000mm | 800mm | 1                | Black Grey | RAL 7021   |
| 21630-090     | 47U         | 2200mm | 800mm | 1                | Black Grey | RAL 7021   |
| 21630-091     | 52U         | 2450mm | 800mm | 1                | Black Grey | RAL 7021   |
| 21630-440     | 24U         | 1200mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-441     | 24U         | 1200mm | 800mm | 1                | Black Grey | RAL 7021   |
| 21630-442     | 29U         | 1400mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-443     | 29U         | 1400mm | 800mm | 1                | Black Grey | RAL 7021   |
| 21630-444     | 33U         | 1600mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-445     | 33U         | 1600mm | 800mm | 1                | Black Grey | RAL 7021   |
| 21630-446     | 38U         | 1800mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-447     | 38U         | 1800mm | 800mm | 1                | Black Grey | RAL 7021   |

| Table 2/2      |                          |               |                   |             |
|----------------|--------------------------|---------------|-------------------|-------------|
| Catalog Number | Complies With            | Finish        | Type              | Works With  |
| 21630-086      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-087      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-088      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-089      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-090      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |

| Catalog Number | Complies With            | Finish        | Type              | Works With  |
|----------------|--------------------------|---------------|-------------------|-------------|
| 21630-091      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-440      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-441      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-442      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-443      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-444      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-445      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-446      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |
| 21630-447      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**