


PXI System With ATX PSU, 4 U, 8 slots, 44 HP

CATALOG NUMBER

14579-008



PXI Desktop Chassis with vertical Card Cage for eight 3 U Boards and built in Power Supply.

CERTIFICATIONS



FEATURES

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11); Backplane, conforms to PICMG rev. 3.0 and PXI 2.0

PXI desktop chassis, 4 U, 44 HP with vertical card cage. Board format Front: 3U, 160 mm

Backplane, 8 slot, 3 HE, 64 bit, System slot left

Heat dissipation with airflow bottom to rear

ATX power supply 400 W, wide-range AC input with power switch on rear

Backplane with clock switching internal / external

PRODUCT ATTRIBUTES

Product Type: System

Number of Slots: 8

Type: Desktop

Backplane Type: 3 U CompactPCI with PXIbus

Data Transfer: 64-bit PCI Bus

Power per Slot: 30W

Input Voltage AC: 100 – 240V

Airflow Direction: Bottom to Rear

Rack Height: 4U

Power Supply Type: Open Frame

Power Supply Included: Yes

Rear I/O: No

Complies With: PXISA PXI-1 R2.0

Depth: 355mm

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Modified systems available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE