

# Socket Strip, UTE

## Data Solutions



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with UTE outlets.

### CERTIFICATIONS



### FEATURES

230 V, 16 A

In accordance with NFC 61-303

Socket strip with UTE sockets

Mounting height 1 U

Horizontal or vertical mounting

Connecting cable 2 m, with SCHUKO/UTE plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

### SPECIFICATIONS

|                      |                     |
|----------------------|---------------------|
| <b>Material:</b>     | Aluminum; Polyamide |
| <b>Color:</b>        | Grey                |
| <b>Product Type:</b> | Socket Strip        |

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Function                                         | Package Quantity |
|----------------|-------------|-----------------|------------------|------------|--------------------------------------------------|------------------|
| 60110-220      | UTE         | 4               | No               | 230V       |                                                  | 1                |
| 60110-221      | UTE         | 9               | No               | 230V       |                                                  | 1                |
| 60110-225      | UTE         | 8               | Yes              | 230V       |                                                  | 1                |
| 60110-267      | UTE         | 6               | No               | 230V       | Transient Protection, Mains Suppression Filter   | 1                |
| 60110-227      | UTE         | 8               | No               | 230V       | Transient Protection                             | 1                |
| 60110-229      | UTE         | 7               | No               | 230V       | Mains Suppression Filter                         | 1                |
| 60110-222      | UTE         | 12              | No               | 230V       |                                                  | 1                |
| 60110-223      | UTE         | 15              | No               | 230V       |                                                  | 1                |
| 60110-224      | UTE         | 19              | No               | 230V       |                                                  | 1                |
| 60110-226      | UTE         | 12              | Yes              | 230V       |                                                  | 1                |
| 60110-228      | UTE         | 6               | No               | 230V       | Overcurrent Protection                           | 1                |
| 60110-230      | UTE         | 6               | No               | 230V       | Fault Current Protection                         | 1                |
| 60110-231      | UTE         | 6               | No               | 230V       | Fault Current Protection, Overcurrent Protection | 1                |

Table 2/2

| Catalog Number | Depth | Finish   | Length  |
|----------------|-------|----------|---------|
| 60110-220      | 44mm  | Anodized | 210mm   |
| 60110-221      | 44mm  | Anodized | 438.5mm |

| Catalog Number | Depth | Finish   | Length  |
|----------------|-------|----------|---------|
| 60110-225      | 44mm  | Anodized | 438.5mm |
| 60110-267      | 44mm  | Anodized | 438.5mm |
| 60110-227      | 44mm  | Anodized | 438.5mm |
| 60110-229      | 44mm  | Anodized | 438.5mm |
| 60110-222      | 44mm  | Anodized | 947.5mm |
| 60110-223      | 44mm  | Anodized | 1202mm  |
| 60110-224      | 44mm  | Anodized | 1753mm  |
| 60110-226      | 44mm  | Anodized | 947.5mm |
| 60110-228      | 75mm  | Anodized | 438.5mm |
| 60110-230      | 88mm  | Anodized | 438.5mm |
| 60110-231      | 88mm  | Anodized | 438.5mm |

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**