


# Board Cage for Horizontal Board Installation



Board cage for horizontal boards offers the option to insert 6 U boards in a 3 or 4 U high subracks or desktop cases. Please add a front front panel to cover the assembly Kit.

## CERTIFICATIONS



## FEATURES

For horizontal mounting of double Euroboards in 3 or 4 U high subracks/cases

## SPECIFICATIONS

**Product Family:** EuropacPRO

**Product Type:** Mounting Kit

**Works With:** Subracks

Table 1/1

| Catalog Number | Rack Height | Rack Width | Package Quantity | Material             | Type                                     | Quick Ship |
|----------------|-------------|------------|------------------|----------------------|------------------------------------------|------------|
| 24564-117      | 3U          | 20HP       | 1                | Aluminum, Zinc Alloy | Horizontal Board Mounting                | No         |
| 24564-217      | 4U          | 28HP       | 1                | Aluminum, Zinc Alloy | Horizontal Board Mounting                | No         |
| 24564-118      | 3U          | 20HP       | 1                | Aluminum, Zinc Alloy | Horizontal Board Mounting, With Long Lip | No         |

ADDITIONAL PRODUCT DETAILS

Please order front frame and EMC shielding material separately.

54 TE space required.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE