nVent | SCHROFF

We connect and protect

Varistar Fan Tray

CATALOG NUMBER

23130-070



Fan Tray allows easy active cooling through fans with IEC320 connection. The Varistar fan tray is ideal for flat top covers with cut out zones.

CERTIFICATIONS

RoHS COMPLIANT

EAC

FEATURES

- Suitable for flat top cover with cut-out zones
- Mounts completely in cabinet interior, no protrusion over top cover
- Mains connection via SCHUKO/UTE plug - IEC 60320 C13 socket
- With three fans, completely wired, connecting cable IEC 320

PRODUCT ATTRIBUTES

- Product Type: Fan Unit
- Product Family: Varistar
- Type: Fan Tray
- Color: Black Grey
- Color Code: RAL 7021
- EMC Shielding: No
- Mounting: Screw-on Front
- Input Voltage AC: 207V
- Depth: 170mm
- Height: 38mm
- Width: 449mm
- Protection Rating: IP20
- Airflow: 410m³/h
- Noise Level: 45dB(A)
- Power: 45W
- Package Quantity: 1
- Finish: Powder Coated
- Material: Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.