

# Varistar CP Glazed Door With 1-Point Locking

## Power Utilities

### FEATURES

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

### SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Width	Locking Type	Color	Color Code
21630-392	24 U	1200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-393	24 U	1200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-481	24 U	1200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-482	24 U	1200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-394	29 U	1400 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-395	29 U	1400 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-483	29 U	1400 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-484	29 U	1400 mm	800 mm	Single Point Locking	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Locking Type	Color	Color Code
21630-396	33 U	1600 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-397	33 U	1600 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-485	33 U	1600 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-486	33 U	1600 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-398	38 U	1800 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-399	38 U	1800 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-487	38 U	1800 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-488	38 U	1800 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-016	42 U	2000 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-017	42 U	2200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-489	42 U	2000 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-490	42 U	2000 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-018	47 U	2000 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-019	47 U	2200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-491	47 U	2200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-492	47 U	2200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021

Table 2/3

Catalog Number	Complies With	Finish	Material	Product Type	Protection Rating	Type
21630-392	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door

CatalogNumber	Complies With	Finish	Material	Product Type	Protection Rating	Type
21630-393	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-481	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-482	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-394	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-395	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-483	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-484	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-396	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-397	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-485	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-486	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-398	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-399	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-487	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-488	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-016	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-017	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-489	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door

CatalogNumber	Complies With	Finish	Material	Product Type	Protection Rating	Type
21630-490	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-018	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-019	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-491	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door
21630-492	IEC 61587-1	Powder Coated	Steel, Glass	Cabinet Door	IP20	Glass Door

Table 3/3

Catalog Number	Works With
21630-392	Varistar CP
21630-393	Varistar CP
21630-481	Varistar CP
21630-482	Varistar CP
21630-394	Varistar CP
21630-395	Varistar CP
21630-483	Varistar CP
21630-484	Varistar CP
21630-396	Varistar CP
21630-397	Varistar CP
21630-485	Varistar CP
21630-486	Varistar CP

Catalog Number	Works With
21630-398	Varistar CP
21630-399	Varistar CP
21630-487	Varistar CP
21630-488	Varistar CP
21630-016	Varistar CP
21630-017	Varistar CP
21630-489	Varistar CP
21630-490	Varistar CP
21630-018	Varistar CP
21630-019	Varistar CP
21630-491	Varistar CP
21630-492	Varistar CP

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**