

CleanTray 90-Degree Elbow



Clean Tray 90-Degree Elbows are used for right-angle installations. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

FEATURES

Clean Tray 90-Degree Elbows are used for right-angle installations

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

SPECIFICATIONS

Finish: Brushed #3
Material: Stainless Steel 304

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
CT22EFC90SS	15734	Elbow	51mm	51mm	1.27mm	No
CT22EFCNT90SS	17765	Elbow	51mm	51mm	1.27mm	No
CT22EIC90SS	15741	Elbow	51mm	51mm	1.27mm	No
CT22EOC90SS	15746	Elbow	51mm	51mm	1.27mm	No
CT22PEFC90SS	16554	Elbow	51mm	51mm	1.27mm	No
CT33EFC90SS	15735	Elbow	76mm	76mm	1.27mm	No
CT33EIC90SS	15742	Elbow	76mm	76mm	1.27mm	No
CT33EOC90SS	15747	Elbow	76mm	76mm	1.27mm	No
CT44EFC90SS	15736	Elbow	102mm	102mm	1.27mm	No
CT44EFCNT90SS	17767	Elbow	102mm	102mm	1.27mm	No
CT44EIC90SS	15743	Elbow	102mm	102mm	1.27mm	No
CT44EOC90SS	15748	Elbow	102mm	102mm	1.27mm	No
CT44PEFC90SS	16556	Elbow	102mm	102mm	1.27mm	No
CT46EFC90SS	15737	Elbow	102mm	152mm	1.27mm	No
CT46EIC90SS	15744	Elbow	102mm	152mm	1.27mm	No
CT46EOC90SS	15751	Elbow	102mm	152mm	1.27mm	No
CT66EFC90SS	15738	Elbow	152mm	152mm	1.27mm	No

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
CT66EFCNT90SS	17771	Elbow	152mm	152mm	1.27mm	No
CT66EIC90SS	15745	Elbow	152mm	152mm	1.27mm	No
CT66EOC90SS	15752	Elbow	152mm	152mm	1.27mm	No
CTS33EFC90SS	16591	Elbow	76mm	76mm	1.27mm	No
CTS33PEFC90SS	16633	Elbow	76mm	76mm	1.27mm	No
CTS44EFC90SS	16592	Elbow	102mm	102mm	1.27mm	No
CTS44PEFC90SS	16634	Elbow	102mm	102mm	1.27mm	No
CTS46EFC90SS	16593	Elbow	102mm	152mm	1.27mm	No
CTS46PEFC90SS	16635	Elbow	102mm	152mm	1.27mm	No
CTS66EFC90SS	16594	Elbow	152mm	152mm	1.27mm	No
CTS66PEFC90SS	16636	Elbow	152mm	152mm	1.27mm	No
CT33EFCNT90SS	17766	Elbow	76mm	76mm	1.27mm	No
CT33PEFC90SS	16555	Elbow	76mm	76mm	1.27mm	No
CT46EFCNT90SS	17768	Elbow	102mm	152mm	1.27mm	No
CT46PEFC90SS	16557	Elbow	102mm	152mm	1.27mm	No
CT66PEFC90SS	16558	Elbow	152mm	152mm	1.27mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE