


Rack Angles 19-inch



19-in. U-Shaped Rack Angles are available in square-hole and tapped-hole designs. Tapped Rack Angles have 10-32 tapped holes. Square-Hole Rack Angles are designed to accept metric or English cage nuts. 19-in. Rack Angles are fixed directly into a 600-mm wide enclosure frame. To mount 19-in. Rack Angles in 700- or 800-mm wide frames, use frame reducing brackets.

FEATURES

Furnished in pairs

Tapped-Hole Rack Angles are constructed from 12 gauge conductive steel, while Square-Hole Rack Angles are 14 gauge conductive steel; U-shaped, channel construction

Tapped-Hole Rack Angles have 10-32 threaded holes; Square-Hole Rack Angles are designed to accept metric or English cage nuts. Comply with ANSI/EIA RS-310-D rack mounting standards.

Rack Angles fit directly into 600-mm wide frames; other widths require Frame Reducing Brackets or Adjustable Rack-Mounting Rails (sold separately).

SPECIFICATIONS

Finish: Plated

Table 1/1						
Catalog Number	Article Number	Material	Rack Units	Hole Type	Thickness	Quick Ship
PRA1914TH	64890	Mild Steel	29U	Square	1.9mm	No
PRA1916TH	64900	Mild Steel	33U	Square	1.9mm	No
PRA1918TH	64910	Mild Steel	38U	Square	1.9mm	No
PRA1920TH	64920	Mild Steel	42U	Square	1.9mm	No
PRA1922TH	64930	Mild Steel	47U	Square	1.9mm	No
PRA197TH	64880	Mild Steel	13U	Square	1.9mm	No
PRA198TH	40259	Mild Steel	16U	Square	1.9mm	No
PRA1914TP	64960	Mild Steel	29U	Tapped	2.66mm	No
PRA1916TP	64970	Mild Steel	33U	Tapped	2.66mm	No
PRA1918TP	64980	Mild Steel	38U	Tapped	2.66mm	No
PRA1920TP	64990	Mild Steel	42U	Tapped	2.66mm	No
PRA1922TP	65120	Mild Steel	47U	Tapped	2.66mm	No
PRA197TP	64950	Mild Steel	13U	Tapped	2.66mm	No
PRA198TP	40269	Mild Steel	16U	Tapped	2.66mm	No

ADDITIONAL PRODUCT DETAILS

Vertical holes spaced in 1.75-in. (44.5-mm) increments.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE