

# Ventilated Bottom Plate, CVB



Can be used in combination with a ventilated plinth PV. 33% ventilated.

## FEATURES

---

Description: Can be used in combination with a ventilated plinth PV. 33% ventilated.

Material: 1.5 mm perforated zinc plated steel.

Pack quantity: 3 pieces, 4 pieces for D>600mm, with mounting material.

Mounting requirements: Use in combination with ventilated plinths PV.

## SPECIFICATIONS

**Thickness:** 1.5mm  
**Finish:** Galvanized  
**Material:** Mild Steel

Table 1/1

| Catalog Number | Article Number | Height | Width  | Depth | Enclosure Material              | Product Family |
|----------------|----------------|--------|--------|-------|---------------------------------|----------------|
| CVB0604        |                | 23mm   | 600mm  | 400mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB0605        |                | 23mm   | 600mm  | 500mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB0606        | CVB0606        | 23mm   | 600mm  | 600mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB0608        | CVB0608        | 23mm   | 600mm  | 800mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB0804        |                | 23mm   | 800mm  | 400mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB0805        |                | 23mm   | 800mm  | 500mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB0806        | CVB0806        | 23mm   | 800mm  | 600mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB0808        | CVB0808        | 23mm   | 800mm  | 800mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB1004        |                | 23mm   | 1000mm | 400mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB1005        |                | 23mm   | 1000mm | 500mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB1006        |                | 23mm   | 1000mm | 600mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB1008        |                | 23mm   | 1000mm | 800mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB1206        | CVB1206        | 23mm   | 1200mm | 600mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |
| CVB1208        | CVB1208        | 23mm   | 1200mm | 800mm | Mild Steel,<br>Galvanized Steel | Free-Standing  |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**