


Varistar Deco Frame Adapter Bracket



Adapter Brackets are helpful in assembling slide rails and shelves for a nopen frame Varistar cabinet with deco frame.

CERTIFICATIONS



FEATURES

For assembling slide rails and shelves in Varistar Deco

SPECIFICATIONS

Product Type:	Bracket
Material:	Steel

Table 1/2

Catalog Number	Rack Height	Height	Package Quantity	Color	Color Code	Finish
23130-234	42U	2000mm	2	Light Grey	RAL 7035	Powder Coated
23130-233	38U	1800mm	2	Light Grey	RAL 7035	Powder Coated
23130-221	29U	1400mm	2	Black Grey	RAL 7021	Powder Coated
23130-223	38U	1800mm	2	Black Grey	RAL 7021	Powder Coated
23130-232	33U	1600mm	2	Light Grey	RAL 7035	Powder Coated
23130-231	29U	1400mm	2	Light Grey	RAL 7035	Powder Coated
23130-224	42U	2000mm	2	Black Grey	RAL 7021	Powder Coated
23130-222	33U	1600mm	2	Black Grey	RAL 7021	Powder Coated
23130-235	47U	2200mm	2	Light Grey	RAL 7035	Powder Coated
23130-230	24U	1200mm	2	Light Grey	RAL 7035	Powder Coated
23130-220	24U	1200mm	2	Black Grey	RAL 7021	Powder Coated
23130-225	47U	2200mm	2	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Type	Width	Works With	Quick Ship
23130-234	Deco Frame Bracket	600mm	Cabinet	No
23130-233	Deco Frame Bracket	600mm	Cabinet	No
23130-221	Deco Frame Bracket	600mm	Cabinet, Varistar CP	No
23130-223	Deco Frame Bracket	600mm	Cabinet, Varistar CP	No

Catalog Number	Type	Width	Works With	Quick Ship
23130-232	Deco Frame Bracket	600mm	Cabinet	No
23130-231	Deco Frame Bracket	600mm	Cabinet	No
23130-224	Deco Frame Bracket	600mm	Cabinet, Varistar CP	No
23130-222	Deco Frame Bracket	600mm	Cabinet, Varistar CP	No
23130-235	Deco Frame Bracket	600mm	Cabinet	No
23130-230	Deco Frame Bracket	600mm	Cabinet	No
23130-220	Bracket	600mm	Varistar, Varistar CP	No
23130-225	Deco Frame Bracket	600mm	Cabinet, Varistar CP	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE