

Varistar CP Side Panel With Quick-Release Fastener and Lock

Varistar Side Panels with Quick-Release Fastener without grounding kit.



FEATURES

Steel, 1 mm

Side panel without grounding kit

Safety lock kit included

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Protection Rating: IP20

Table 1/2

Catalog Number	Rack Height	Height	Depth	Package Quantity	Color	Color Code
21630-285	24U	1200mm	600mm	2	Black Grey	RAL 7021
21630-286	24U	1200mm	800mm	2	Black Grey	RAL 7021
21630-289	29U	1400mm	600mm	2	Black Grey	RAL 7021
21630-290	29U	1400mm	800mm	2	Black Grey	RAL 7021
21630-293	33U	1600mm	600mm	2	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Depth	Package Quantity	Color	Color Code
21630-294	33U	1600mm	800mm	2	Black Grey	RAL 7021
21630-297	38U	1800mm	600mm	2	Black Grey	RAL 7021
21630-298	38U	1800mm	800mm	2	Black Grey	RAL 7021
21630-302	42U	2000mm	600mm	2	Black Grey	RAL 7021
21630-303	42U	2000mm	800mm	2	Black Grey	RAL 7021
21630-304	42U	2000mm	900mm	2	Black Grey	RAL 7021
21630-064	42U	2000mm	1000mm	2	Black Grey	RAL 7021
21630-306	47U	2200mm	600mm	2	Black Grey	RAL 7021
21630-307	47U	2200mm	800mm	2	Black Grey	RAL 7021
21630-308	47U	2200mm	900mm	2	Black Grey	RAL 7021
21630-070	47U	2200mm	1000mm	2	Black Grey	RAL 7021
21630-287	24U	1200mm	900mm	2	Black Grey	RAL 7021
21630-288	24U	1200mm	1000mm	2	Black Grey	RAL 7021
21630-291	29U	1400mm	900mm	2	Black Grey	RAL 7021
21630-292	29U	1400mm	1000mm	2	Black Grey	RAL 7021
21630-295	33U	1600mm	900mm	2	Black Grey	RAL 7021
21630-296	33U	1600mm	1000mm	2	Black Grey	RAL 7021
21630-299	38U	1800mm	900mm	2	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Depth	Package Quantity	Color	Color Code
21630-300	38U	1800mm	1000mm	2	Black Grey	RAL 7021
21630-065	42U	2000mm	1100mm	2	Black Grey	RAL 7021
21630-066	42U	2000mm	1200mm	2	Black Grey	RAL 7021
21630-071	47U	2200mm	1100mm	2	Black Grey	RAL 7021
21630-072	47U	2200mm	1200mm	2	Black Grey	RAL 7021

Table 2/2				
Catalog Number	Finish	Material	Type	Quick Ship
21630-285	Powder Coated	Steel	Side Panel, Quick Release	No
21630-286	Powder Coated	Steel	Side Panel, Quick Release	No
21630-289	Powder Coated	Steel	Side Panel, Quick Release	No
21630-290	Powder Coated	Steel	Side Panel, Quick Release	No
21630-293	Powder Coated	Steel	Side Panel, Quick Release	No
21630-294	Powder Coated	Steel	Side Panel, Quick Release	No
21630-297	Powder Coated	Steel	Side Panel, Quick Release	No
21630-298	Powder Coated	Steel	Side Panel, Quick Release	No
21630-302	Powder Coated	Steel	Side Panel, Quick Release	No
21630-303	Powder Coated	Steel	Side Panel, Quick Release	No
21630-304	Powder Coated	Steel	Side Panel, Quick Release	No
21630-064	Powder Coated	Steel	Side Panel, Quick Release	No

Catalog Number	Finish	Material	Type	Quick Ship
21630-306	Powder Coated	Steel	Side Panel, Quick Release	No
21630-307	Powder Coated	Steel	Side Panel, Quick Release	No
21630-308	Powder Coated	Steel	Side Panel, Quick Release	No
21630-070	Powder Coated	Steel	Side Panel, Quick Release	No
21630-287	Powder Coated	Steel	Side Panel, Quick Release	No
21630-288	Powder Coated	Steel	Side Panel, Quick Release	No
21630-291	Powder Coated	Steel	Side Panel, Quick Release	No
21630-292	Powder Coated	Steel	Side Panel, Quick Release	No
21630-295	Powder Coated	Steel	Side Panel, Quick Release	No
21630-296	Powder Coated	Steel	Side Panel, Quick Release	No
21630-299	Powder Coated	Steel	Side Panel, Quick Release	No
21630-300	Powder Coated	Steel	Side Panel, Quick Release	No
21630-065	Powder Coated	Steel	Side Panel, Quick Release	No
21630-066	Powder Coated	Steel	Side Panel, Quick Release	No
21630-071	Powder Coated	Steel	Side Panel, Quick Release	No
21630-072	Powder Coated	Steel	Side Panel, Quick Release	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE