

CleanTray 45-Degree Elbow



Clean Tray 45-Degree Elbows are used for continuous runs with 45-degree turns. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

FEATURES

Clean Tray 45-Degree Elbows are used for continuous runs with 45-degree turns

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

SPECIFICATIONS

Finish: Brushed #3
Material: Stainless Steel 304

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
CT22EFC45SS	15765	Elbow	51mm	51mm	1.27mm	No
CT33EFC45SS	15766	Elbow	76mm	76mm	1.27mm	No
CT33EIC45SS	15754	Elbow	76mm	76mm	1.27mm	No
CT33EOC45SS	15761	Elbow	76mm	76mm	1.27mm	No
CT44EFC45SS	15767	Elbow	102mm	102mm	1.27mm	No
CT44EIC45SS	15755	Elbow	102mm	102mm	1.27mm	No
CT44EOC45SS	15762	Elbow	102mm	102mm	1.27mm	No
CT44PEFC45SS	16563	Elbow	102mm	102mm	1.27mm	No
CT46EFC45SS	15768	Elbow	102mm	152mm	1.27mm	No
CT46EIC45SS	15756	Elbow	102mm	152mm	1.27mm	No
CT46EOC45SS	15763	Elbow	102mm	152mm	1.27mm	No
CT66EFC45SS	15771	Elbow	152mm	152mm	1.27mm	No
CT66EOC45SS	15764	Elbow	152mm	152mm	1.27mm	No
CTS33EFC45SS	16595	Elbow	76mm	76mm	1.27mm	No
CTS33PEFC45SS	16637	Elbow	76mm	76mm	1.27mm	No
CTS44EFC45SS	16596	Elbow	102mm	102mm	1.27mm	No
CTS44PEFC45SS	16638	Elbow	102mm	102mm	1.27mm	No

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
CTS46EFC45SS	16597	Elbow	102mm	152mm	1.27mm	No
CTS46PEFC45SS	16641	Elbow	102mm	152mm	1.27mm	No
CTS66EFC45SS	16598	Elbow	152mm	152mm	1.27mm	No
CTS66PEFC45SS	16642	Elbow	152mm	152mm	1.27mm	No
CT22EIC45SS	15753	Elbow	51mm	51mm	1.27mm	No
CT22EOC45SS	15758	Elbow	51mm	51mm	1.27mm	No
CT22PEFC45SS	16561	Elbow	51mm	51mm	1.27mm	No
CT33PEFC45SS	16562	Elbow	76mm	76mm	1.27mm	No
CT46PEFC45SS	16564	Elbow	102mm	152mm	1.27mm	No
CT66EIC45SS	15757	Elbow	152mm	152mm	1.27mm	No
CT66PEFC45SS	16565	Elbow	152mm	152mm	1.27mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE