

# Raystat EX-02 Mechanical Thermostat



nVent RAYCHEM Raystat-EX-02 is a hazardous area mechanical surface sensing thermostat providing temperature control for heating cables. Switching temperature range -4 °C to 163 °C, adjustable externally to the Ex enclosure by a dial mounted under a bolted-on cover and seal. Switching current capacity is 22 A.

## FEATURES

Simple to install and operate: supplied with 3 m long stainless steel fluid filled bulb and capillary, single cable entry through 3/4" NPT thread with nVent RAYCHEM cable glands available to suit non-armoured/armoured cables

Energy saving, line-sensing electronic control thermostat

Adjustable set point: -4 °C to 163 °C (externally to the Ex enclosure by dial mounted under bolted-on cover and seal)

Direct switching, maximum current 16 A, 230 VAC: single pole change-over with volt-free contacts, SPDT

Lightweight cast aluminium with stainless steel fittings, can be pipe mounted using nVent RAYCHEM support brackets or surface mounted

## SPECIFICATIONS

Table 1/2

Catalog Number	Item Name	Material	Thermostat Type	Current Rating	Controller Temperature Setting	Height
404385-000	RAYSTAT-EX-02	Aluminium	Mechanical Thermostat	22 A	-4 to 163 °C	167 mm

Table 2/2

Catalog Number	Item Name	Width	Depth
404385-000	RAYSTAT-EX-02	114.5 mm	101.5 mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**