

# Tray Handle

The tray handle can be clip into a cutout in the side panel of a case. 2 sizes available.



## CERTIFICATIONS



## FEATURES

Static load-carrying capacity 30 kg/pair

Side panel thickness min. 1,0 mm

## SPECIFICATIONS

<b>Static Load:</b>	30kg
<b>Color:</b>	Black
<b>Works With:</b>	Cases
<b>Product Family:</b>	RatiopacPRO; RatiopacPRO AIR; PropacPRO; CompacPRO; Comptec
<b>Product Type:</b>	Handle
<b>Material:</b>	Polycarbonate
<b>Type:</b>	Static

Table 1/2

Catalog Number	Height	Width	Depth	Package Quantity	Handle Type	Flammability Rating
60225-012	79mm	187mm	22mm	1	Tray Handle	UL® 94V-0

CatalogNumber	Height	Width	Depth	Package Quantity	Handle Type	Flammability Rating
60229-004	56mm	110mm	18mm	1	Tray Handle	UL® 94V-0

Table 2/2

Catalog Number	Quick Ship
60225-012	No
60229-004	No

## ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**