

# Front Panel, Unshielded, With Fastener Pin

## Power Utilities



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

### CERTIFICATIONS



### FEATURES

Enable grounding of the front area (protection class 1)

### SPECIFICATIONS

Table 1/3

Catalog Number	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
20119-161	21 HP	1	Screw-on Front	Anodized	Conductive	No
20119-163	42 HP	1	Screw-on Front	Anodized	Anodized	No
20119-162	28 HP	1	Screw-on Front	Anodized	Conductive	No
20119-160	14 HP	1	Screw-on Front	Anodized	Conductive	No

CatalogNumber	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
20119-159	7 HP	1	Screw-on Front	Anodized	Conductive	No

Table 2/3

Catalog Number	Complies With	EMC Shielding	Height	Material	Product Type	Rack Height
20119-161	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel	3 U
20119-163	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel	3 U
20119-162	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel	3 U
20119-160	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel	3 U
20119-159	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel	3 U

Table 3/3

Catalog Number	Type	Width
20119-161	Front Panel without Handle	106.3 mm
20119-163	Front Panel without Handle	213 mm
20119-162	Front Panel without Handle	141.9 mm
20119-160	Front Panel without Handle	70.8 mm
20119-159	Front Panel without Handle	35.2 mm

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**