


Novastar Steel Door



CERTIFICATIONS



FEATURES

St, 1.5 mm

Opening angle 180°, incl. grounding

Can be assembled at front and rear

Lock (2233x) with key

SPECIFICATIONS

Width:	553mm
Product Type:	Cabinet Door
Material:	Steel

Table 1/2

Catalog Number	Color	Color Code	Finish	Height	Package Quantity	Rack Height
25230-020	Black Grey	RAL 7021	Powder Coated	323mm	1	6U
25230-021	Black Grey	RAL 7021	Powder Coated	422mm	1	9U
25230-022	Black Grey	RAL 7021	Powder Coated	555mm	1	12U
25230-023	Black Grey	RAL 7021	Powder Coated	733mm	1	16U
25230-024	Black Grey	RAL 7021	Powder Coated	911mm	1	20U
25230-025	Black Grey	RAL 7021	Powder Coated	1133mm	1	25U
25230-026	Black Grey	RAL 7021	Powder Coated	1534mm	1	34U
25230-027	Black Grey	RAL 7021	Powder Coated	1711mm	1	38U
25230-028	Black Grey	RAL 7021	Powder Coated	1933mm	1	43U
25230-029	Black Grey	RAL 7021	Powder Coated	2111mm	1	47U
25230-030	Black Grey	RAL 7021	Powder Coated	1345mm	1	29U
26230-020	Light Grey	RAL 7035	Powder Coated	323mm	1	6U
26230-021	Light Grey	RAL 7035	Powder Coated	422mm	1	9U
26230-022	Light Grey	RAL 7035	Powder Coated	555mm	1	12U
26230-023	Light Grey	RAL 7035	Powder Coated	733mm	1	16U
26230-024	Light Grey	RAL 7035	Powder Coated	911mm	1	20U
26230-025	Light Grey	RAL 7035	Powder Coated	1133mm	1	25U
26230-026	Light Grey	RAL 7035	Powder Coated	1534mm	1	34U

CatalogNumber	Color	Color Code	Finish	Height	Package Quantity	Rack Height
26230-027	Light Grey	RAL 7035	Powder Coated	1711mm	1	38U
26230-028	Light Grey	RAL 7035	Powder Coated	1933mm	1	43U
26230-029	Light Grey	RAL 7035	Powder Coated	2111mm	1	47U
26230-030	Light Grey	RAL 7035	Powder Coated	1345mm	1	29U

Table 2/2

Catalog Number	Type	Quick Ship
25230-020	Steel Door	No
25230-021	Steel Door	No
25230-022	Steel Door	No
25230-023	Steel Door	No
25230-024	Steel Door	No
25230-025	Steel Door	No
25230-026	Steel Door	No
25230-027	Steel Door	No
25230-028	Steel Door	No
25230-029	Steel Door	No
25230-030	Steel Door	No
26230-020	Steel Door	No
26230-021	Steel Door	No

Catalog Number	Type	Quick Ship
26230-022	Steel Door	No
26230-023	Steel Door	No
26230-024	Steel Door	No
26230-025	Steel Door	No
26230-026	Steel Door	No
26230-027	Steel Door	No
26230-028	Steel Door	No
26230-029	Steel Door	No
26230-030	Steel Door	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE