

Transparent Aluminium Doors, ADA



Components mounted on the enclosure door are protected by the viewing window, but can be easily operated by opening only the viewing window, while the enclosure door can remain closed. The components are protected from the environment and from undesired operations when the viewing window is closed.

FEATURES

Description: Viewing window when used in combination with mounting kit ADAMK. The double-bit 3 mm lock can be replaced by any optional insert or handle. It increases the enclosure depth by 10 mm.

Material: Aluminium and 3 mm acrylic glass.

Finish: Anodised aluminium.

Protection: Complies with IP 54.

Pack quantity: 1 viewing window.

To replace the standard door

Can be used in combination with swing frame, modular chassis or inner door

The double-bit 3 mm lock can be replaced by any optional insert or handle

It increases the enclosures depth by 10 mm (ADA) or 35 mm (ADAB)

Can also be used as a viewing window when used in combination with mounting kit ADAMK/ADABMK

Includes mounting hardware

Number of locks: 1

SPECIFICATIONS

Material: Aluminum

Finish: Mill

Table 1/1

Catalog Number	E-Number	Height	Width	Depth	Latch Quantity	Window Size
ADA03030	2502118	300mm	300mm	30mm	1	226 x 226mm
ADA04030	2502119	400mm	300mm	30mm	1	326 x 226mm
ADA04040	2502120	400mm	400mm	30mm	1	326 x 326mm
ADA04060	2502121	400mm	600mm	30mm	1	326 x 526mm
ADA05030	2502122	500mm	300mm	30mm	1	426 x 226mm
ADA05040	2502123	500mm	400mm	30mm	1	426 x 326mm
ADAB06040	2502124	600mm	400mm	30mm	2	522 x 322mm
ADAB06060	2502125	600mm	600mm	30mm	2	522 x 522mm
ADAB06080	2502126	600mm	800mm	30mm	2	522 x 722mm
ADAB07050	2502127	700mm	500mm	30mm	2	622 x 422mm
ADAB08060	2502128	800mm	600mm	30mm	2	722 x 522mm
ADAB10080	2502129	1000mm	800mm	30mm	2	922 x 722mm
ADAB12060	2502130	1200mm	600mm	30mm	2	1122 x 522mm
ADAB12080	2502131	1200mm	800mm	30mm	2	1122 x 722mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE