

# Varistar CP Seismic Base Plate, IP55 and EMC, One-Piece

## Power Utilities

The base plate is solid and covers the base of the cabinet.

### FEATURES

The base plate is solid and covers the base of the cabinet

Is assembled from outside

### SPECIFICATIONS

Table 1/2

| Catalog Number | Width  | Depth   | Color      | Color Code | Complies With                                             | Material |
|----------------|--------|---------|------------|------------|-----------------------------------------------------------|----------|
| 20630-309      | 600 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Steel    |
| 20630-310      | 600 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Steel    |
| 20630-311      | 600 mm | 1000 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Steel    |
| 20630-312      | 600 mm | 1200 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Steel    |
| 20630-313      | 800 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Steel    |

| CatalogNumber | Width  | Depth   | Color      | Color Code | Complies With                                             | Material |
|---------------|--------|---------|------------|------------|-----------------------------------------------------------|----------|
| 20630-314     | 800 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Steel    |
| 20630-315     | 800 mm | 1000 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Steel    |
| 20630-316     | 800 mm | 1200 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Steel    |

Table 2/2

| Catalog Number | Product Type      | Protection Rating | Type              | Works With  |
|----------------|-------------------|-------------------|-------------------|-------------|
| 20630-309      | Cabinet/Rack Base | IP55              | Base Plate, Plain | Varistar CP |
| 20630-310      | Cabinet/Rack Base | IP55              | Base Plate, Plain | Varistar CP |
| 20630-311      | Cabinet/Rack Base | IP55              | Base Plate, Plain | Varistar CP |
| 20630-312      | Cabinet/Rack Base | IP55              | Base Plate, Plain | Varistar CP |
| 20630-313      | Cabinet/Rack Base | IP55              | Base Plate, Plain | Varistar CP |
| 20630-314      | Cabinet/Rack Base | IP55              | Base Plate, Plain | Varistar CP |
| 20630-315      | Cabinet/Rack Base | IP55              | Base Plate, Plain | Varistar CP |
| 20630-316      | Cabinet/Rack Base | IP55              | Base Plate, Plain | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

This base plate is used for applications which don't require cable entry from the base.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**