

## Plug-In Unit Kit With IEL Handle, Shielded, Black 3 U, 12 HP

**CATALOG NUMBER**

**20848-591**



Plug-in unit, with IEL inserter/extractor black handle, 3 U, front assembly. The U-shaped front panel enable shielding with a textile gasket.

## CERTIFICATIONS




## FEATURES

|                                                                                         |
|-----------------------------------------------------------------------------------------|
| U-shaped front panel for textile gasket                                                 |
| Suitable for insertion and extraction forces up to 700 N (per pair)                     |
| Enable the installation of a microswitch                                                |
| Enable the installation of coding pegs in accordance with IEC 60297-3-103/ IEEE 1101.10 |

## PRODUCT ATTRIBUTES

|                                                                               |
|-------------------------------------------------------------------------------|
| Rack Width: 12HP                                                              |
| Package Quantity: 1                                                           |
| Handle Type: IEL                                                              |
| Mounting: Screw-on Front                                                      |
| Gasket Type: Textile EMC                                                      |
| Front Finish: Anodized                                                        |
| Rear Finish: Etched                                                           |
| Treated Edges: No                                                             |
| Complies With: IEC 60297-3-102; IEEE 1101.10; IEC 60297-3-103; IEEE 1101.1/11 |
| EMC Shielding: Yes                                                            |
| Finish: Anodized; Passivated                                                  |
| Height (H): 128.4mm                                                           |
| Material: Aluminum                                                            |
| Product Type: Front Panel                                                     |
| Rack Height: 3U                                                               |
| Type: Front Panel with Handle (PIU)                                           |
| Width (W): 60.6mm                                                             |
| Gross Weight: 0.118kg                                                         |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**