



## Horizontal Rail, Rear, Type H-ST, Heavy, Standard, 42 HP

**CATALOG NUMBER**

**34560-542**



### Combinations of horizontal rails and side panels

|                                                                                                                                  |  | + = can be combined. |                                                  | - = combination: not recommended                                               |   |
|----------------------------------------------------------------------------------------------------------------------------------|--|----------------------|--------------------------------------------------|--------------------------------------------------------------------------------|---|
| <br>Alu-Profile<br>Alu-Profile<br>Alu-Profile |  | -                    | +                                                | +                                                                              | + |
|                                                                                                                                  |  | +                    | aluminum foil flexible<br>aluminum foil flexible | aluminum foil flexible and<br>aluminum foil flexible<br>aluminum foil flexible |   |
| <br>Alu-Profile<br>Alu-Profile                |  | +                    | +                                                | +                                                                              | + |
|                                                                                                                                  |  | +                    | aluminum foil flexible                           | aluminum foil flexible                                                         |   |
| <br>Alu-Profile<br>Alu-Profile                |  | +                    | +                                                | -                                                                              | - |
|                                                                                                                                  |  | +                    | aluminum foil flexible                           | aluminum foil flexible                                                         |   |
| <br>Alu-Profile<br>Alu-Profile                |  | +                    | +                                                | -                                                                              | - |
|                                                                                                                                  |  | +                    | aluminum foil flexible                           | aluminum foil flexible                                                         |   |
| <br>Alu-Profile<br>Alu-Profile                |  | +                    | +                                                | -                                                                              | - |
|                                                                                                                                  |  | +                    | aluminum foil flexible                           | aluminum foil flexible                                                         |   |
| <br>Alu-Profile<br>Alu-Profile                |  | +                    | +                                                | -                                                                              | - |
|                                                                                                                                  |  | +                    | aluminum foil flexible                           | aluminum foil flexible                                                         |   |
| <br>Alu-Profile<br>Alu-Profile                |  | +                    | +                                                | -                                                                              | - |
|                                                                                                                                  |  | +                    | aluminum foil flexible                           | aluminum foil flexible                                                         |   |

The horizontal rail, type ST enables the isolated assembly of a backplane. The isolation is done by an insulation strip.

## CERTIFICATIONS



## FEATURES

### For indirect backplane mounting with insulation strip

Standard where mechanical demands are high (H-ST)

## Mounting top and bottom

< 28 HP not printed

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUCT ATTRIBUTES

|                                                                                |
|--------------------------------------------------------------------------------|
| Rack Width: 42HP                                                               |
| Package Quantity: 1                                                            |
| Finish: Anodized                                                               |
| Length: 218.44mm                                                               |
| Material: Aluminum                                                             |
| Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO |
| Product Type: Horizontal Rail                                                  |
| Type: Heavy, ST                                                                |
| Works With: Subracks; Cases                                                    |

ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

|                                                                                                                                       |                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                 |                                                                                                                                                                                                                                               |
|---------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>North America</b><br>All locations<br>+1.763.422.2661<br>Chat with us:<br><a href="http://nvent.com/schroff">nvent.com/schroff</a> | <b>Europe</b><br>Straubenhardt, Germany<br>+49.7082.794.0<br>Betschdorf, France<br>+33.3.88.90.64.90<br>Warsaw, Poland<br>+48.22.209.98.35<br>Assago, Italy<br>+39.02.932.7141<br>Chat with us:<br><a href="http://nvent.com/schroff">nvent.com/schroff</a> | <b>Asia</b><br>Shanghai, China<br>+86.21.2412.6943<br>Qingdao, China<br>+86.532.8771.6101<br>Singapore<br>+65.6768.5800<br>Shin-Yokohama, Japan<br>+81.45.476.0271<br>Chat with us:<br><a href="http://nvent.com/schroff">nvent.com/schroff</a> | <b>Middle East &amp; India</b><br>Dubai, United Arab Emirates<br>+971.4.378.1700<br>Bangalore, India<br>+91.80.6715.2001<br>Istanbul, Turkey<br>+90.216.250.7374<br>Chat with us:<br><a href="http://nvent.com/schroff">nvent.com/schroff</a> |
|---------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE