

# Varistar CP Base Plate, One-Piece

## Power Utilities

The base plate is solid and covers the base of the cabinet.

### FEATURES

The base plate is solid and covers the base of the cabinet

Is assembled from outside

### SPECIFICATIONS

Table 1/2

| Catalog Number | Width  | Depth   | Protection Rating | Color      | Color Code | Complies With |
|----------------|--------|---------|-------------------|------------|------------|---------------|
| 21630-320      | 600 mm | 300 mm  |                   | Black Grey | RAL 7021   |               |
| 21630-628      | 600 mm | 300 mm  |                   | Black Grey | RAL 7021   |               |
| 21630-322      | 600 mm | 600 mm  |                   | Black Grey | RAL 7021   |               |
| 21630-323      | 600 mm | 800 mm  |                   | Black Grey | RAL 7021   |               |
| 21630-324      | 600 mm | 900 mm  |                   | Black Grey | RAL 7021   |               |
| 21630-325      | 600 mm | 1000 mm |                   | Black Grey | RAL 7021   |               |
| 21630-326      | 600 mm | 1100 mm |                   | Black Grey | RAL 7021   |               |
| 21630-327      | 600 mm | 1200 mm |                   | Black Grey | RAL 7021   |               |
| 21630-629      | 600 mm | 600 mm  |                   | Black Grey | RAL 7021   |               |

| CatalogNumber | Width  | Depth   | Protection Rating | Color      | Color Code | Complies With               |
|---------------|--------|---------|-------------------|------------|------------|-----------------------------|
| 21630-630     | 600 mm | 800 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-631     | 600 mm | 900 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-632     | 600 mm | 1000 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-633     | 600 mm | 1100 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-634     | 600 mm | 1200 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-826     | 600 mm | 600 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-827     | 600 mm | 800 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-828     | 600 mm | 900 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-829     | 600 mm | 1000 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-830     | 600 mm | 1100 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-831     | 600 mm | 1200 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-330     | 800 mm | 600 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-635     | 800 mm | 600 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-832     | 800 mm | 600 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-331     | 800 mm | 800 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-332     | 800 mm | 900 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-333     | 800 mm | 1000 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-334     | 800 mm | 1100 mm |                   | Black Grey | RAL 7021   |                             |

| CatalogNumber | Width  | Depth   | Protection Rating | Color      | Color Code | Complies With               |
|---------------|--------|---------|-------------------|------------|------------|-----------------------------|
| 21630-335     | 800 mm | 1200 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-636     | 800 mm | 800 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-637     | 800 mm | 900 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-638     | 800 mm | 1000 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-639     | 800 mm | 1100 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-640     | 800 mm | 1200 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-833     | 800 mm | 800 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-834     | 800 mm | 900 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-835     | 800 mm | 1000 mm |                   | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-836     | 800 mm | 1100 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-837     | 800 mm | 1200 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |

Table 2/2

| Catalog Number | Material | Product Type      | Works With |
|----------------|----------|-------------------|------------|
| 21630-320      | Steel    | Cabinet/Rack Base |            |
| 21630-628      | Steel    | Cabinet/Rack Base |            |
| 21630-322      | Steel    | Cabinet/Rack Base |            |
| 21630-323      | Steel    | Cabinet/Rack Base |            |
| 21630-324      | Steel    | Cabinet/Rack Base |            |
| 21630-325      | Steel    | Cabinet/Rack Base |            |

| Catalog Number | Material | Product Type      | Works With  |
|----------------|----------|-------------------|-------------|
| 21630-326      | Steel    | Cabinet/Rack Base |             |
| 21630-327      | Steel    | Cabinet/Rack Base |             |
| 21630-629      | Steel    | Cabinet/Rack Base |             |
| 21630-630      | Steel    | Cabinet/Rack Base |             |
| 21630-631      | Steel    | Cabinet/Rack Base |             |
| 21630-632      | Steel    | Cabinet/Rack Base |             |
| 21630-633      | Steel    | Cabinet/Rack Base |             |
| 21630-634      | Steel    | Cabinet/Rack Base |             |
| 21630-826      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-827      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-828      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-829      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-830      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-831      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-330      | Steel    | Cabinet/Rack Base |             |
| 21630-635      | Steel    | Cabinet/Rack Base |             |
| 21630-832      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-331      | Steel    | Cabinet/Rack Base |             |

| Catalog Number | Material | Product Type      | Works With  |
|----------------|----------|-------------------|-------------|
| 21630-332      | Steel    | Cabinet/Rack Base |             |
| 21630-333      | Steel    | Cabinet/Rack Base |             |
| 21630-334      | Steel    | Cabinet/Rack Base |             |
| 21630-335      | Steel    | Cabinet/Rack Base |             |
| 21630-636      | Steel    | Cabinet/Rack Base |             |
| 21630-637      | Steel    | Cabinet/Rack Base |             |
| 21630-638      | Steel    | Cabinet/Rack Base |             |
| 21630-639      | Steel    | Cabinet/Rack Base |             |
| 21630-640      | Steel    | Cabinet/Rack Base |             |
| 21630-833      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-834      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-835      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-836      | Steel    | Cabinet/Rack Base | Varistar CP |
| 21630-837      | Steel    | Cabinet/Rack Base | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

This base plate is used for applications which don't require cable entry from the base.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**