

4G24 Twist Clip with Stud



CERTIFICATIONS



FEATURES

Supports electrical fixtures from acoustical T-grid

No tools required for installation

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid

Nut sold separately

SPECIFICATIONS

Material: Spring Steel;Steel

Table 1/2


Catalog Number	Article Number	E-Number	Finish	Color	Screw Length (L)	Flange Thickness (FT)
4G24M16WHSP 25	172290	1511441	Painted	White	16mm	1.5 mm
4G24M11WH	171840	1500755	Painted	White	11mm	1.5 mm

CatalogNumber	Article Number	E-Number	Finish	Color	Screw Length (L)	Flange Thickness (FT)
4G24M25WHSP 25	172300	1511442	Painted	White	25mm	1.5 mm
4G24M16	171710	1511432	nVent CADDY Armour	Gray	16mm	1.5 mm
4G24M25	171730	1511433	nVent CADDY Armour	Gray	25mm	1.5 mm
4G24M11	171680	1511431	nVent CADDY Armour	Gray	11mm	1.5 mm
4G24M16WH	171860		Painted	White	16mm	1.5 mm

Table 2/2

Catalog Number	Article Number	E-Number	T-Grid Size	Screw Diameter (Sc)	Static Load
4G24M16WHSP25	172290	1511441	24mm	6	220N
4G24M11WH	171840	1500755	24mm	6	220N
4G24M25WHSP25	172300	1511442	24mm	6	220N
4G24M16	171710	1511432	24mm	6	220N
4G24M25	171730	1511433	24mm	6	220N
4G24M11	171680	1511431	24mm	6	220N
4G24M16WH	171860		24mm	6	220N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

