


# Mounting Plates For Power Distribution, MSMPN



The mounting plate, MSMPN, for fix and modular systems, can be easily machined and have components mounted on it before fixed within the relevant compartment.

## FEATURES

Description: Mounting plate for installation of breakers. Suitable for left and right hand connections.

Material: 1.5 mm galvanized steel.

Pack quantity: 1 piece with mounting material.

Mounting requirements: To be assembled on the modular system frame with MSMPA01 or MSMPF01.

SPECIFICATIONS

Finish: Plated  
Material: Steel

| Table 1/1      |        |       |                    |                     |             |                    |
|----------------|--------|-------|--------------------|---------------------|-------------|--------------------|
| Catalog Number | Height | Width | Type               | Fits Enclosure Size | Panel Size  | Enclosure Material |
| MSMPN1008H     | 10mm   | 800mm | Horizontal Opening | 100 x 800mm         | 96 x 670mm  | Mild Steel         |
| MSMPN0506      | 50mm   | 600mm | Plain              | 50 x 600mm          | 496 x 470mm | Mild Steel         |
| MSMPN0508      | 50mm   | 800mm | Plain              | 50 x 800mm          | 496 x 670mm | Mild Steel         |
| MSMPN1006      | 100mm  | 600mm | Plain              | 100 x 600mm         | 96 x 470mm  | Mild Steel         |
| MSMPN1006H     | 100mm  | 600mm | Horizontal Opening | 100 x 600mm         | 96 x 470mm  | Mild Steel         |
| MSMPN1008      | 100mm  | 800mm | Plain              | 100 x 800mm         | 96 x 670mm  | Mild Steel         |
| MSMPN1506      | 150mm  | 600mm | Plain              | 150 x 600mm         | 146 x 470mm | Mild Steel         |
| MSMPN1506V     | 150mm  | 600mm | Vertical Opening   | 150 x 600mm         | 146 x 470mm | Mild Steel         |
| MSMPN1508      | 150mm  | 800mm | Plain              | 150 x 800mm         | 146 x 670mm | Mild Steel         |
| MSMPN1508V     | 150mm  | 800mm | Vertical Opening   | 150 x 800mm         | 146 x 670mm | Mild Steel         |
| MSMPN2006      | 200mm  | 600mm | Plain              | 200 x 600mm         | 196 x 470mm | Mild Steel         |
| MSMPN2006V     | 200mm  | 800mm | Vertical Opening   | 200 x 600mm         | 196 x 470mm | Mild Steel         |
| MSMPN2008      | 250mm  | 600mm | Plain              | 200 x 800mm         | 196 x 670mm | Mild Steel         |
| MSMPN2008V     | 200mm  | 800mm | Vertical Opening   | 200 x 800mm         | 196 x 670mm | Mild Steel         |
| MSMPN2506      | 250mm  | 600mm | Plain              | 250 x 600mm         | 246 x 470mm | Mild Steel         |
| MSMPN2506V     | 250mm  | 600mm | Vertical Opening   | 250 x 600mm         | 246 x 470mm | Mild Steel         |
| MSMPN2508      | 250mm  | 800mm | Plain              | 250 x 800mm         | 246 x 670mm | Mild Steel         |

| Catalog Number | Height | Width  | Type             | Fits EnclosureSize | Panel Size  | EnclosureMaterial |
|----------------|--------|--------|------------------|--------------------|-------------|-------------------|
| MSMPN2508V     | 250mm  | 800mm  | Vertical Opening | 250 x 800mm        | 246 x 670mm | Mild Steel        |
| MSMPN3006      | 300mm  | 600mm  | Plain            | 300 x 600mm        | 296 x 470mm | Mild Steel        |
| MSMPN3006V     | 300mm  | 600mm  | Vertical Opening | 300 x 600mm        | 296 x 470mm | Mild Steel        |
| MSMPN3008      | 300mm  | 800mm  | Plain            | 300 x 800mm        | 296 x 670mm | Mild Steel        |
| MSMPN3008V     | 300mm  | 800mm  | Vertical Opening | 300 x 800mm        | 296 x 670mm | Mild Steel        |
| MSMPN4006      | 400mm  | 600mm  | Plain            | 400 x 600mm        | 396 x 470mm | Mild Steel        |
| MSMPN4006V     | 400mm  | 600mm  | Vertical Opening | 400 x 600mm        | 396 x 470mm | Mild Steel        |
| MSMPN4008      | 400mm  | 800mm  | Plain            | 400 x 800mm        | 396 x 670mm | Mild Steel        |
| MSMPN4008V     | 400mm  | 800mm  | Vertical Opening | 400 x 800mm        | 396 x 670mm | Mild Steel        |
| MSMPN4506      | 450mm  | 600mm  | Plain            | 450 x 600mm        | 446 x 470mm | Mild Steel        |
| MSMPN4506V     | 450mm  | 600mm  | Vertical Opening | 450 x 600mm        | 446 x 470mm | Mild Steel        |
| MSMPN4508      | 450mm  | 800mm  | Plain            | 450 x 800mm        | 446 x 670mm | Mild Steel        |
| MSMPN4508V     | 450mm  | 800mm  | Vertical Opening | 450 x 800mm        | 446 x 670mm | Mild Steel        |
| MSMPN5006      | 500mm  | 600mm  | Plain            | 500 x 600mm        | 496 x 470mm | Mild Steel        |
| MSMPN5008      | 500mm  | 800mm  | Plain            | 500 x 800mm        | 496 x 670mm | Mild Steel        |
| MSMPN6006      | 600mm  | 600mm  | Plain            | 600 x 600mm        | 596 x 470mm | Mild Steel        |
| MSMPN6006V     | 600mm  | 600mm  | Vertical Opening | 600 x 600mm        | 596 x 470mm | Mild Steel        |
| MSMPN6008      | 600mm  | 800mm  | Plain            | 600 x 800mm        | 596 x 670mm | Mild Steel        |
| MSMPN6008V     | 600mm  | 1000mm | Vertical Opening | 600 x 800mm        | 596 x 670mm | Mild Steel        |
| MSMPN6010      | 600mm  | 1000mm | Plain            | 600 x 1000mm       | 596 x 870mm | Mild Steel        |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**