

Front/Rear Plinth Base, PFS



This stainless steel plinth allows for cabling without any restrictions. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

FEATURES

Description: Front and rear plinth sections. For cabling without any restrictions and in accordance with the VDE 0113 standard. The plinth consists of four corner pieces with removable front covers. The side panels PSS are to be ordered separately. Produced in 100 mm and 200 mm heights. 200 mm high plinths are delivered with a rear cover for cabling that consists of two removable panels 100 mm high. The front cover is a one piece panel of 200 mm high. All panels have double returns on each panel for added strength.

Material: AISI 304 / AISI 316L pre-grained stainless steel. Corners 2 mm and panels 1.5 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1x front plinth and 1x rear plinth with mounting accessories.

Mounting requirements: Add the side panels PSS for a complete plinth.

SPECIFICATIONS

Thickness: 1.5mm

Finish: Brushed

Table 1/1

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Product Family
PFS1120	2514276	100mm	1200mm	60mm	Mild Steel	Free-Standing
PFS2120	2514280	200mm	1200mm	60mm	Mild Steel	Free-Standing
PFS1080	2514274	100mm	800mm	60mm	Mild Steel	Free-Standing
PFS2080	2514278	200mm	800mm	60mm	Mild Steel	Free-Standing
PFS1060	2514273	100mm	600mm	60mm	Mild Steel	Free-Standing
PFS2060	2514277	200mm	600mm	60mm	Mild Steel	Free-Standing
PFS1100	2514275	100mm	1000mm	60mm	Mild Steel	Free-Standing
PFS2100	2514279	200mm	1000mm	60mm	Mild Steel	Free-Standing
PFS1060-316	2503390	100mm	600mm	60mm	Mild Steel	Free-Standing
PFS1080-316	2503391	100mm	800mm	60mm	Mild Steel	Free-Standing
PFS1100-316	2503392	100mm	1000mm	60mm	Mild Steel	Free-Standing
PFS1120-316	2503393	100mm	1200mm	60mm	Mild Steel	Free-Standing
PFS2060-316	2503394	200mm	600mm	60mm	Mild Steel	Free-Standing
PFS2080-316	2503395	200mm	800mm	60mm	Mild Steel	Free-Standing
PFS2100-316	2503396	200mm	1000mm	60mm	Mild Steel	Free-Standing
PFS2120-316	2503397	200mm	1200mm	60mm	Mild Steel	Free-Standing

ADDITIONAL PRODUCT DETAILS

For enclosures 1600 mm wide use 2 x 800 mm wide plinth.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE