nVent SCHROFF

We connect and protect

19" Fan Unit, 1 U, Remote Control and Monitoring, 6 Fans, 100-240 VAC

CATALOG NUMBER

10713-554

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

CERTIFICATIONS

CE

FEATURES

- Fan speed temperature controlled
- ModBus Interface for Remote Monitoring and Control
- Temperature threshold for the fan control adjustable on the front panel
- Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs
- Integrated power supply with wide range input (100 V – 240 V)
- Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer
- 2 NTC temperature sensors with Cables included

PRODUCT ATTRIBUTES

- Product Type: Fan Unit
- Input Voltage AC: 100 – 240V
- Airflow: 1089m³/h

Noise Level: 59.5dB(A)

Power: 97W

Max Static Pressure: 78Pa

Ambient Temperature: –10 to 70°C

Lifespan, L10 @ 40 C: 99558h

Package Quantity: 1

Finish: Aluminum-Zinc Plated; Anodized

Material: Steel; Aluminum

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.