


Cable to Web of Rail Mold Pair, Power

Data Solutions



FEATURES

Replacement mold pair designed for the installation of track circuits and jumper bonds to the neutral axis

Sold in pairs

SPECIFICATIONS

Material: Graphite

Bond Terminal Style: W

Table 1/1

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBWX201	85 lb to 141 lb T-Rail Sections	35 mm ² Ropelay	7.75mm	T20
PBWX301	UIC60	50 mm ² Concentric	8.89mm	T20
PBW2C	85 lb to 141 lb T-Rail Sections	1/0 Concentric	9.47mm	T20
PBW2G	85 lb to 141 lb T-Rail Sections	2/0 Concentric	10.62mm	T20

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBW2E	85 lb to 141 lb T-Rail Sections	1/0 Ropelay	10.87mm	T20
PBW2J	85 lb to 141 lb T-Rail Sections	2/0 Ropelay	12.19mm	T20
PBWX5	85 lb to 141 lb T-Rail Sections	95 mm ² Ropelay	12.83mm	T20
PBW2Q	85 lb to 141 lb T-Rail Sections	4/0 Concentric	13.41mm	T20
PBW9F	85 lb to 141 lb T-Rail Sections	19/#9 Copperweld	14.53mm	T20
PBW2S	85 lb to 141 lb T-Rail Sections	4/0 Ropelay	15.49mm	T20
PBXLWX5	85 lb to 141 lb T-Rail Sections	95 mm ² Ropelay	15.52mm	T20
PBWX7	85 lb to 141 lb T-Rail Sections	150 mm ² Ropelay	16mm	T20
PBWS7	85 lb to 141 lb T-Rail Sections	4/0 Composite	16.66mm	T20
PBW3D	85 lb to 141 lb T-Rail Sections	350 kcmil Concentric	17.3mm	T20
PBWX8	85 lb to 141 lb T-Rail Sections	185 mm ² Ropelay	17.8mm	T20
PBW2W	85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	T20
PBW2W135	135 lb Bethlehem	250 kcmil Ropelay	19.05mm	T20
PBW2W20AS	20 lb ASCE	250 kcmil Ropelay	19.05mm	T20
PBW2W40AS	40 lb ASCE	250 kcmil Ropelay	19.05mm	T20
PBW3B	85 lb to 141 lb T-Rail Sections	300 kcmil Ropelay	20.32mm	T20
PBW3S	85 lb to 141 lb T-Rail Sections	500 kcmil Ropelay	26.42mm	T20
PBW3SZU160	ZU160 Rail	500 kcmil Ropelay	26.42mm	T20

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE