


# Varistar CP Seismic Base Plate, IP55 and EMC, One-Piece

The base plate is solid and covers the base of the cabinet.



## FEATURES

The base plate is solid and covers the base of the cabinet

Is assembled from outside

## SPECIFICATIONS

|                           |                    |
|---------------------------|--------------------|
| <b>Product Type:</b>      | Cabinet/Rack Base  |
| <b>Finish:</b>            | Hot-Dip Galvanized |
| <b>Protection Rating:</b> | IP55               |
| <b>Material:</b>          | Steel              |

Table 1/2

| Catalog Number | Width | Depth | Package Quantity | Complies With                                             | Type                 | Works With  |
|----------------|-------|-------|------------------|-----------------------------------------------------------|----------------------|-------------|
| 20630-309      | 600mm | 600mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Base Plate,<br>Plain | Varistar CP |
| 20630-310      | 600mm | 800mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Base Plate,<br>Plain | Varistar CP |

| CatalogNumber | Width | Depth  | Package Quantity | Complies With                                             | Type                 | Works With  |
|---------------|-------|--------|------------------|-----------------------------------------------------------|----------------------|-------------|
| 20630-311     | 600mm | 1000mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Base Plate,<br>Plain | Varistar CP |
| 20630-312     | 600mm | 1200mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Base Plate,<br>Plain | Varistar CP |
| 20630-313     | 800mm | 600mm  | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Base Plate,<br>Plain | Varistar CP |
| 20630-314     | 800mm | 800mm  | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Base Plate,<br>Plain | Varistar CP |
| 20630-315     | 800mm | 1000mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Base Plate,<br>Plain | Varistar CP |
| 20630-316     | 800mm | 1200mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Base Plate,<br>Plain | Varistar CP |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
| 20630-309      | No         |
| 20630-310      | No         |
| 20630-311      | No         |
| 20630-312      | No         |
| 20630-313      | No         |
| 20630-314      | No         |
| 20630-315      | No         |

| Catalog Number | Quick Ship |
|----------------|------------|
| 20630-316      | No         |

## ADDITIONAL PRODUCT DETAILS

This base plate is used for applications which don't require cable entry from the base.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**